

Mini DVI to DVI Cable Adapter, Video Converter for Macbooks and iMacs, 1920x1200 (Mini DVI to DVI-D M/F)

MODEL NUMBER: **P138-000-DVI**



Highlights

- Connect a DVI Monitor to Apple Intel iMac, MacBook, and 12in PowerBook G4 mini-DVI Port
- 8 in. overall length
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- Apple Intel iMac, MacBook, and 12in PowerBook G4

Package Includes

- 8-in. mini-DVI to DVI-D Adapter

Description

Tripp Lite's mini-DVI to DVI-D Digital Female Video Adapter Cable allows you to connect a DVI-D Display to the mini-DVI port found on some Apple computer models. Supports Single Link digital transmission, with resolutions up to 1920x1200@60Hz.

Features

- Connect a DVI Monitor to Apple Intel iMac, MacBook, and 12-in. PowerBook G4 mini-DVI Port
- 8 in. overall length
- 1920x1200 @ 60Hz resolution
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
Chromebook Compatible	No
Display Style	Adapter
Model Type	DVI
Cable Types	DVI
INPUT	
Cable Length (ft.)	0.7
Cable Length (in.)	8



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	White
CONNECTIONS	
Connector A	MINI-DVI (MALE)
Connector B	DVI-D DUAL LINK (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.