

Mini DVI to VGA Cable Adapter, Video Converter for Macbooks and iMacs (M/F)

MODEL NUMBER: **P138-000-VGA**



Highlights

- Connect a VGA Monitor to an Apple Intel iMac, MacBook, or 12-inch PowerBook G4 mini-DVI Port
- 8-inch overall length

System Requirements

- Apple Intel iMac, MacBook, or 12-inch PowerBook G4

Package Includes

8-inch mini-DVI to VGA Adapter

Description

Tripp Lites mini-DVI to VGA Female Video Adapter Cable allows you to connect a VGA Display to the mini-DVI port found on some Apple computer models. Supports resolutions up to 1920 x 1080 (1080i).

Features

- Connect a VGA Monitor to an Apple Intel iMac, MacBook, or 12-inch PowerBook G4 mini-DVI Port
- 8-inch overall length
- Supports video resolutions up to 1920 x 1080 (1080i)

Specifications

OVERVIEW	
Chromebook Compatible	No
Display Style	Adapter
Model Type	VGA
Cable Types	VGA
INPUT	
Cable Length (ft.)	0.7
Cable Length (in.)	8
PHYSICAL	
Color	White



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Connector A	MINI-DVI (MALE)
Connector B	HD15 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.