

HDMI Right Angle Up Adapter / Coupler (M/F)

MODEL NUMBER: **P142-000-UP**



Highlights

- Use in tight spaces where cables would not ordinarily fit
- Saves wear and tear on equipment ports and cable ends

System Requirements

- Video equipment with HDMI video out ports

Package Includes

- HDMI Male to Female Right Angle adapter

Description

The 90-degree angle of this adapter allows you to reposition the HDMI jack for better access where space is tight. This adapter also offers a great way to protect your HDMI cables and equipment from strain and damage, since HDMI cables have relatively small connectors and jacks that must bear the brunt of the cable's weight. The plug-and-play design makes installation a breeze. The P142-000-UP Right Angle HDMI Adapter features gold-plated connectors for optimal signal transmission quality. Provides clean, uncompressed digital signals. Supports video resolution up to 1080p. Ver 1.3 and 1.4 compliant.

Features

- HDMI Male Plug
- HDMI Female Jack
- One inch deep when plugged into video port
- Supports v1.3 / v1.4, 1080p, 1080i, 720p

Specifications

OVERVIEW	
Chromebook Compatible	Yes
Style	HDMI
Display Style	Adapter
Model Type	HDMI
Cable Types	HDMI
PHYSICAL	
Color	Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Connector A	HDMI (FEMALE)
Connector B	HD15 (MALE) - RIGHT ANGLE
CERTIFICATIONS	
Certifications	Tested to
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.