

HDMI Display-Side Wallplate with Active Signal Booster, White (F/F)

MODEL NUMBER: **P166-001-A**



Description

Tripp Lite's P166-001-A HDMI Display-side Wallplate with Signal Booster increases the distance a 1080p (24Hz) signal can be transmitted beyond the recommended 16 ft. (5 m.). It supports video resolutions up to 1080p, and a maximum distance of 150 ft. from the source. Use P568-Series HDMI cables in most applications. When extending a 1080p (24Hz) signal more than 75 ft., use cable made with 24Awg wiring, such as the [P568-100-HD](#). (Lengths over 100 ft. are available from Tripp Lite as a custom order) 24Awg HDMI cable is also needed when extending a 3D signal more than 50 ft.. A 3D signal can be extended up to 125 ft. using 24Awg HDMI cable. Simply connect the longer cable between the source and the P166-001-A, and the shorter cable (16 ft. or less) between the adapter and the monitor. Software or drivers are not required. HDCP compliant.

Features

- Cleans up Home Theater installations by hiding HDMI Cables
- Wallplate is the size of a standard electrical outlet
- Extend a 1080p (24Hz) HDMI signal up to 150 ft. from the source
- Use P568-Series HDMI cables in most applications
- When extending a 1080p (24Hz) signal more than 75 ft., use cable made with 24Awg wiring, such as the [P568-100-HD](#). (Lengths over 100 ft. are available from Tripp Lite as a custom order)
- 24Awg HDMI cable is also needed when extending a 3D signal more than 50 ft.. A 3D signal can be extended up to 125 ft. using 24Awg HDMI cable
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- HDCP compliant
- No software or drivers required

Specifications

Highlights

- Extend a 1080p (24Hz) HDMI signal up to 150 ft. from the source
- When extending a 1080p (24Hz) signal more than 75 ft., use cable made with 24Awg wiring, such as the [P568-100-HD](#)
- 24Awg HDMI cable is also needed when extending a 3D signal more than 50 ft.. A 3D signal can be extended up to 125 ft. using 24Awg HDMI cable
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio

Applications

- For use when HDMI source equipment is located beyond the 16 ft. (5 m.) distance limitation.

Package Includes

- HDMI Display-side Wallplate w/Signal Booster



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
Chromebook Compatible	Yes
Display Style	Signal Booster
Model Type	HDMI
Accessories Type	Wall Plate
PHYSICAL	
Color	White
CONNECTIONS	
Connector A	HDMI (FEMALE)
Connector B	HDMI (FEMALE)
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.