

VGA Coax Monitor Easy Pull Extension Cable, High Resolution Cable with RGB Coax (HD15 M/F), 100-ft

MODEL NUMBER: **P501-100**



Description

Tripp Lite's 100 ft. SVGA/VGA Easy Pull Monitor Extension Cable w/ Connectors makes running long length video cables a snap. The pull-apart design allows the cable to be run through conduit or other tight areas that a HD15 connector wouldn't fit through. Diameter of the circular DIN end is only 7/8". Circular Easy Pull connector is threaded to ensure maximum security once the cable is reattached. The mini-coax (RGB) and paired video wire construction delivers superior signal quality. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both the high density DB15 male and high density DB15 female connectors are molded and have integral strain relief to ensure they last a long time.

Features

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- Superior-molded cables with foil and braid shielding for maximum EMI/RFI protection
- RGB 75-ohm coax construction for maximum video resolution
- HD15 male to HD15 female molded connectors
- Supports resolutions up to 1600 x 1200

Specifications

OVERVIEW	
Chromebook Compatible	No
Style	Video Cables
Display Style	Easy Pull
Model Type	VGA

Highlights

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- 75ohm mini-coax (RGB) and paired video wire construction delivers outstanding signal quality
- Superior-molded cables with foil and braid shielding for maximum EMI/RFI protection

Applications

- Suspended ceilings, walls, conduit or anywhere too small to fit a standard HD15 cable during installation.

Package Includes

- 100 ft. Male/Female Easy Pull SVGA/VGA Monitor Extension Cable w/ Connectors
- Wallplate with HD15 cutout



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Types	MONITOR
INPUT	
Cable Length (ft.)	100
Cable Length (m)	30.48
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	HD15 (MALE)
Connector B	HD15 (FEMALE)
CERTIFICATIONS	
Certifications	RoHS-Compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.