

Low Profile VGA Coax Monitor Cable, High Resolution Cable with RGB Coax (HD15 M/M), 10-ft.

MODEL NUMBER: **P502-010-SM**



Highlights

- Slim, compact SVGA / VGA Male-Male Cable , 10-ft
- 40% thinner cable than standard VGA Cables
- More compact molded ends
- Supports up to 2048x1536 Resolution

Package Includes

- 10-ft, Compact SVGA / VGA M/M Monitor Cable

Description

Tripp Lite's 10-ft, PVC, SVGA / VGA Compact monitor replacement cable, features a 40% reduced diameter cable, and smaller molded connectors. The mini-coax (RGB) and paired video wire construction delivers superior video signal quality, up to 2048x1536. Nickel plated connectors and gold plated copper contacts ensure excellent conductivity. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both high density DB15 male connectors are molded and have integral strain relief to ensure long life.

Features

- Slim, compact SVGA / VGA Male - Male Cable, 10-ft
- 40% thinner cable than standard VGA Cables
- Smaller, more compact, molded ends than standard VGA cables
- Supports up to 2048x1536 Resolution
- Foil and Braid shielded for superior noise suppression

Specifications

OVERVIEW	
Chromebook Compatible	No
Style	Monitor Cables
Model Type	VGA
Cable Types	MONITOR
INPUT	
Cable Length (ft.)	10



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	3.05
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	HD15 (MALE) - LOW PROFILE
Connector B	HD15 (MALE) - LOW PROFILE
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.