

## VGA Coax Right-Angle Monitor Cable, High Resolution Cable with RGB Coax (HD15 M/M), 25-ft.

MODEL NUMBER: **P502-025-RA**



### Highlights

- Right Angle connection at one end for tight spaces
- 75ohm Coax conductors for RGB signals
- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- Resolutions up to 2048 x 1536

### Package Includes

25-ft. SVGA/VGA Monitor Cable Right Angle HD15M to Straight HD15M Gold Connectors w/ RGB Coax

### Description

Tripp Lite's 25 foot SVGA/VGA Right Angle monitor replacement cable is the gold standard in video cables. One end features a super-slim right angle connection for tight spaces, i.e., behind a PC. The mini-coax (RGB) and paired video wire construction delivers superior signal quality. Gold plated connectors and gold plated copper contacts ensure excellent conductivity. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both high density DB15 male connectors are molded and have integral strain relief to ensure they last a lifetime.

### Features

- Right Angled connection for installations with space constraints
- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality.
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity.
- Right Angle HD15 male to Straight HD15 male molded connectors
- Resolutions up to 2048 x 1536

## Specifications

OVERVIEW	
Chromebook Compatible	No
Style	Monitor Cables
Display Style	Cable
Model Type	VGA
Cable Types	MONITOR



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

INPUT	
Cable Length (ft.)	25
Cable Length (m)	7.62
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	HD15 (MALE) - RIGHT ANGLE
Connector B	HD15 (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.