

VGA Coax Monitor Cable, High Resolution Cable with RGB Coax (HD15 M/M) 30-ft.

MODEL NUMBER: **P502-030**



Highlights

- 30ft SVGA/VGA Male-Male Cable
- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Resolutions up to 2048 X 1536

Description

Tripp Lite's 30-foot SVGA/VGA monitor replacement cable is the gold standard in video cables. The mini-coax (RGB) and paired video wire construction delivers superior signal quality. Gold plated connectors and gold plated copper contacts ensure excellent conductivity. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both high density DB15 male connectors are molded and have integral strain relief to ensure they last a long time.

Features

- 30ft SVGA/VGA Male-Male Cable
- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Resolutions up to 2048 X 1536
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality.
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity.
- HD15 male to HD15 male molded connectors

Specifications

OVERVIEW	
Chromebook Compatible	No
Style	Monitor Cables
Model Type	VGA
Cable Types	MONITOR
INPUT	
Cable Length (ft.)	30



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	9.14
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	HD15 (MALE)
Connector B	HD15 (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.