

## VGA Coax Monitor Cable with Audio, High Resolution Cable with RGB Coax (HD15 and 3.5mm M/M) 6-ft.

MODEL NUMBER: **P504-006**



### Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- CMR PVC rated
- 3.5mm Stereo Plugs

### Package Includes

- 6-ft. SVGA/VGA Monitor Cable HD15M to HD15M w/Built-in Audio connectors

### Description

Tripp Lite's 6 foot PVC SVGA/VGA monitor replacement cable features built-in 3.5mm stereo plugs, for extending audio as well video. The mini-coax (RGB) and paired video wire construction delivers superior video signal quality. Nickel plated connectors and gold plated copper contacts ensure excellent conductivity. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both high density DB15 male connectors are molded and have integral strain relief to ensure they last a long time.

### Features

- Extend both Video and Audio signals
- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality.
- HD15 male to HD15 male molded connectors
- Computer side Audio Pigtail: 8in Display side Audio Pigtail: 24in

## Specifications

OVERVIEW	
Chromebook Compatible	No
Style	Monitor Cables
Display Style	Cable
Model Type	VGA
INPUT	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Cable Length (ft.)	6
Cable Length (m)	1.83
<b>PHYSICAL</b>	
Color	Black
<b>CONNECTIONS</b>	
Connector A	HD15 (MALE) & 3.5MM (MALE)
Connector B	HD15 (MALE) & 3.5MM (MALE)
Connector C	HD15 (MALE)
Connector D	3.5MM (MALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.