

Low-Profile VGA Coax Monitor Cable with Audio, High Resolution Cable with RGB Coax (HD15 and 3.5mm M/M), 6-ft.

MODEL NUMBER: **P504-006-SM**



Highlights

- Slim, compact SVGA / VGA Male-Male Cable with Audio, 6ft
- 40% thinner cable than standard VGA Cables
- More compact molded ends
- Supports up to 2048x1536 Resolution

Package Includes

- 6-ft, Compact SVGA / VGA M/M Monitor Cable with Audio Cable

Description

Tripp Lite's 6-ft, PVC, SVGA / VGA Compact monitor replacement cable, features a 40% reduced diameter cable, smaller molded connectors, and built-in 3.5mm stereo plugs, for extending audio as well as video. The mini-coax (RGB) and paired video wire construction delivers superior video signal quality, up to 2048x1536. Nickel plated connectors and gold plated copper contacts ensure excellent conductivity. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both high density DB15 male connectors are molded and have integral strain relief to ensure long life.

Features

- Slim, compact SVGA / VGA Male - Male Cable with Audio, 6ft
- 40% thinner cable than standard VGA Cables
- Smaller, more compact, molded ends than standard VGA cables
- Supports up to 2048x1536 Resolution
- 22-inch Audio 3.5mm Stereo pigtails
- Foil and Braid shielded for superior noise suppression

Specifications

OVERVIEW	
Chromebook Compatible	No
Style	Monitor Cables
Display Style	Cable
Model Type	VGA
Cable Types	MONITOR



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.83
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	HD15 (MALE) (LOW PROFILE) & 3.5MM (MALE)
Connector B	HD15 (MALE) (LOW PROFILE) & 3.5MM (MALE)
Connector C	HD15 (MALE)
Connector D	3.5MM (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.