

VGA Monitor Cable, 640x480 (HD15 M/M), 6-ft.

MODEL NUMBER: P512-006



Highlights

 Superior molded cables with foil-shielding for maximum EMI/RFI protection

System Requirements

• Monitor with removable HD15 cable and resolutions up to 640x480.

Package Includes

 6-ft. VGA Monitor Cable HD15M to HD15M Gold Connectors

Description

Tripp Lite's VGA monitor replacement cable is designed for use with a monitor that has a removable cable with HD15 connectors. This 6 foot cable has gold plated connectors and gold plated copper contacts to ensure excellent conductivity. Shielded for maximum EMI/RFI protection. The HD15 male and HD15 male connectors are molded and have integral strain relief to ensure they last a long time.

For use with monitors with resolutions up to 640x480 (VGA Std). For higher resolution monitors, please use P502-006.

Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- HD15 male to HD15 male molded connectors

Specifications

OVERVIEW	
Chromebook Compatible	No
Style	Monitor Cables
Display Style	Cable
Model Type	VGA
Cable Types	MONITOR
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.83



PHYSICAL		
Color	Black	
CONNECTIONS		
Connector A	HD15 (MALE)	
Connector B	HD15 (MALE)	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.