

DVI to VGA Monitor Cable, High Resolution Cable with RGB Coax (DVI-A to HD15 M/M), 10-ft.

MODEL NUMBER: **P556-010**



Description

Tripp Lite's 10-ft. DVI to HD15 cable allows PC users with a DVI-I port to connect to monitors with a VGA connector. Gold-plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Both the DVI and HD15 connectors are molded and have integral strain relief for long life reliability.

Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality
- Gold plated copper contacts ensure excellent conductivity
- DVI Male to HD15 Male molded connectors
- PC and Mac compatible
- Meets DVI DDWG Standard
- Supports analog signal only

Specifications

OVERVIEW	
Chromebook Compatible	No
Style	DVI
Display Style	Adapter
Model Type	VGA
Cable Types	DVI

Highlights

- Connects a DVI-I port on a computer to a monitor with a VGA connector
- Compatible with Flat-Panel Displays, Digital CRT Displays and Projectors
- Supports analog signals only
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Meets DVI DDWG Standard

System Requirements

- PC with DVI-I connector, and Monitor with SVGA (HD15F) connector

Package Includes

10ft, DVI-I MALE to VGA Male Adapter Cable



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

INPUT	
Cable Length (ft.)	10
Cable Length (m)	3.05
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	DVI-A (MALE)
Connector B	HD15 (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.