

DVI Single Link Cable, Digital TMDS Monitor Cable (DVI-D M/M), 25-ft.

MODEL NUMBER: **P561-025**



Highlights

- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Resolutions up to 1920 x 1200
- High Speed Digital Transmission to 4.95Gbps

System Requirements

- Monitor with DVI, and CPU with a DVI video card

Package Includes

DVI Single Link TMDS cable - DVI-D, M/M, 25-ft.

Description

Tripp Lite's 25-ft. DVI Single Link TMDS cable delivers the high performance, high bandwidth needed for today's digital video displays. Gold plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Both DVI connectors are molded and have integral strain relief for long life reliability.

Features

- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Single Link digital signaling for transmission speeds to 4.95Gbps and 1920 x 1200 resolution
- Gold plated contacts ensure excellent conductivity
- Meets DVI DDWG Standard
- For use with Digital CRT displays, Flat Panel Displays, HDTV and Projectors

Specifications

OVERVIEW	
Chromebook Compatible	No
Style	DVI
Display Style	Cable
Model Type	DVI
Cable Types	DVI
INPUT	
Cable Length (ft.)	25



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	7.62
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	DVI-D SINGLE LINK (MALE)
Connector B	DVI-D SINGLE LINK (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.