

DVI Dual Link Digital Extension Adapter Cable with 45 degree Left Plug (DVI-D M/F), 1-ft.

MODEL NUMBER: **P562-001-45L**



Highlights

- For use with Single or Dual TMDS Link specified equipment
- Ideal for use in tight spaces
- Saves wear and tear on your equipment connector
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection

System Requirements

- Digital Video card or Monitor with a DVI-D connector.

Package Includes

- DVI Dual Link 45 Degree Left Extension Cable, DVI-D M/F, 1FT

Description

Tripp Lite's 1 foot DVI-D Male to DVI-D Female adapter cable is the ideal solution for those tight spaces where a standard straight DVI cable will not fit. The adapter also saves wear and tear on your video cards connector. This cable features Gold connectors and contacts, fully molded ends, and double-shielded cable.

Features

- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Dual Link digital signalling for transmission speeds to 9.9Gbps
- Gold plated copper contacts ensure excellent conductivity
- Meets DVI DDWG Standard
- PC and Mac compatible
- For use with Digital CRT displays, Flat Panel Displays, HDTV and Projectors

Specifications

OVERVIEW	
Chromebook Compatible	No
Style	DVI
Display Style	Cable
Model Type	DVI
Cable Types	DVI
INPUT	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (ft.)	1
Cable Length (m)	0.30
PHYSICAL	
Color	Black
CONNECTIONS	
Side A - Connector 1	DVI-D DUAL LINK (MALE) - 45 DEGREES
Side B - Connector 1	DVI-D DUAL LINK (FEMALE)
CERTIFICATIONS	
Certifications	RoHS Compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.