

DisplayPort Cable with Latches (M/M) 25-ft.

MODEL NUMBER: P580-025



Highlights

- Digital Video and Audio in one cable
- Supports 1080p resolution
- Small footprint compared to VGA or DVI

Package Includes

DisplayPort Monitor Cable - 25ft

Description

DisplayPort is a new digital display interface standard put forth by the Video Electronics Standards Association (VESA). It defines a digital audio/video interconnect intended to be used between computer and display monitors, or computers and home theater systems. Similar to HDMI, in that it supports both Digital Video/Audio signals, DisplayPort is geared more toward the computer market, where HDMI dominates the Home Theater market. Tripp Lite's DisplayPort cables support a maximum bandwidth of 10.8Gbps, as well as DPCP (DisplayPort Content Protection), HDCP, and resolutions up to 1080p.

Features

- The future standard for Digital Video and Audio connections
- Supports Displayport v1.2
- Provides up to 1080p resolution
- Monitor Resolution Support: 2560x1600 @ 60Hz, 1920x1200 @ 120Hz
- Supports High Definition Content Protection (HDCP)

Specifications

OVERVIEW		
Chromebook Compatible	No	
Style	DisplayPort Cables	
Model Type	DisplayPort	
Cable Types	DISPLAYPORT	
INPUT		
Cable Length (ft.)	25	
Cable Length (m)	7.62	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL		
Color	Black	
CONNECTIONS		
Connector A	DISPLAYPORT (MALE)	
Connector B	DISPLAYPORT (MALE)	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.