

## DisplayPort Cable with Latches (M/M) 30-ft.

MODEL NUMBER: **P580-030**



### Highlights

- Digital Video and Audio in one cable
- Supports Displayport v1.2
- Monitor Resolution Support:  
2560x1600 @ 60Hz, 1920x1200 @ 120Hz
- Small footprint compared to VGA or DVI

### Package Includes

DisplayPort Monitor Cable - 30-ft

### Description

DisplayPort is a digital display interface standard put forth by the Video Electronics Standards Association (VESA). It defines a digital audio/video interconnect intended to be used between computer and display monitors, or computers and home theater systems. Similar to HDMI, in that it supports both Digital Video/Audio signals, DisplayPort is geared more toward the computer market, where HDMI dominates the Home Theater market. Tripp Lite's DisplayPort cables support a maximum bandwidth of 10.8Gbps, as well as DPCP ( DisplayPort Content Protection), and HDCP.

### Features

- The future standard for Digital Video and Audio connections
- Supports Displayport v1.2
- Monitor Resolution Support: 2560x1600 @ 60Hz, 1920x1200 @ 120Hz
- Supports High Definition Content Protection ( HDCP )
- 28AWG, Aluminum/Mylar Shielding

## Specifications

OVERVIEW	
Chromebook Compatible	No
Style	DisplayPort Cables
Display Style	Cable
Model Type	DisplayPort
Cable Types	DISPLAYPORT
INPUT	
Cable Length (ft.)	30



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Cable Length (m)	9.14
<b>PHYSICAL</b>	
Color	Black
<b>CONNECTIONS</b>	
Connector A	DISPLAYPORT (MALE)
Connector B	DISPLAYPORT (MALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.