

eSatA, SatA-II External Signal Shielded Cable (7Pin/7Pin), 36-in.

MODEL NUMBER: **P950-36I**



Description

Tripp Lite expands its line of hard drive cables with the introduction of our new line of eSATA (SATA II) cables.

This 36" data cable connects any high speed eSATA drive, PVR/DVR, or SETOP box to an eSATA controller.

SATA-II delivers higher data transfer rates (up to 6 Gbps), and the double-shielded cable design is perfect for the new generation of External SATA -II drives.

SATA-II drives offer 6 times the transfer rate of USB & Firewire external drives. These cables feature 7-pin straight latching (Male) and offer easy installation.

Features

- Connect your high-speed eSATA device to an eSATA controller
- Support data transfer rates of up to 6 Gbps
- 36" Cable is double-shielded to protect against EMI/RFI
- RoHS Compliant

Specifications

OVERVIEW	
Style	SATA
Cable Types	SATA
INPUT	
Cable Length (ft.)	3
Cable Length (in.)	36
PHYSICAL	

Highlights

- Connect your high-speed eSATA device to a eSATA controller
- Support data transfer rates of up to 6Gbps
- Cable is double-shielded to protect against EMI/RFI

Applications

- External eSATA devices, such as Hard Drives, PVR/DVR's, or SETOP boxes to a eSATA controller card

System Requirements

- eSATA Device
- eSATA Controller

Package Includes

36inch (3ft) eSATA (SATA-II)
 External Signal Cable (7Pin/7Pin)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color	Blue
CONNECTIONS	
Connector A	7 PIN ESATA (MALE)
Connector B	7 PIN ESATA (MALE)
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.