

SatA to eSatA Transition Cable (7Pin/7Pin), 2-ft.

MODEL NUMBER: **P952-002**



Highlights

- Connect external eSATA drives to your SATA internal controller card
- 2ft SATA-II rated 6Gbps cable
- Plug-n-Play
- 7pin SATA "L" type connector (Internal) to 7pin "I" type connector (external)

Description

With Tripp Lite's P952-002, SATA to eSATA bracket/cable, you can connect an external eSATA hard drive to your internal SATA controller. Simply plug the standard 7-pin SATA connector into an available port on your controller card or motherboard, and the bracket into an available external I/O slot. No software to load...completely plug and play. 24" cable provides plenty of length to connect any where inside a PC case. 26AWG cable rated to handle current 6Gbps SATA speeds.

Features

- Connect external eSATA drives to your SATA internal controller card
- SATA-II rated 6Gbps, 24", 26AWG cable
- Plug-n-Play
- 7pin SATA "L" type connector (Internal) to 7pin "I" type connector (external)

Specifications

OVERVIEW	
Style	SATA
Cable Types	SATA
INPUT	
Cable Length (ft.)	2
Cable Length (m)	0.61
PHYSICAL	
Color	Red



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Connector A	7 PIN SATA (MALE)
Connector B	7 PIN ESATA (MALE)
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.