

SatA to eSatA Transition Cable (7Pin/7Pin), 3-ft.

MODEL NUMBER: **P952-003**



Highlights

- SATA Internal "L" to External eSATA "I" Cable - 3-ft.
- Supports data transfer rates of up to 6.0 Gbps
- Cable is shielded to protect against EMI/RFI line noise

Package Includes

- SATA to eSATA Transition Cable - 3-ft.

Description

Tripp Lite's SATA to eSATA Transition Cable allows new eSATA devices to be connected to older style SATA ports. Cable is optimized for data storage with up to 6 Gbps transfer rate.

Features

- SATA Internal "L" to External eSATA "I" Data Cable - 3-ft.
- Supports data transfer rates up to 6 Gbps
- Fully shielded cable to protect against EMI/RFI line noise

Specifications

OVERVIEW	
Style	SATA
Cable Types	SATA
INPUT	
Cable Length (ft.)	3
Cable Length (m)	0.91
PHYSICAL	
Color	Red
CONNECTIONS	
Connector A	7 PIN SATA (MALE)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Connector B	7 PIN ESATA (MALE)
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.