

SatA to eSatA Transition Cable (7Pin/7Pin), 18-in.

MODEL NUMBER: **P952-18I**



Highlights

- SATA Internal "L" to External eSATA "I" Cable - 18 in.
- Supports data transfer rates of up to 6.0 Gbps
- Cable is shielded to protect against EMI/RFI line noise

Package Includes

- SATA to eSATA Transition Cable - 18 in.

Description

Tripp Lite's SATA to eSATA Transition Cable allows new eSATA devices to be connected to older style SATA ports. Cable is optimized for data storage with up to 6Gbps transfer rate.

Features

- SATA Internal "L" to External eSATA "I" Data Cable - 18 in.
- Supports data transfer rates up to 6Gbps
- Fully shielded cable to protect against EMI/RFI line noise

Specifications

| OVERVIEW | |
|--------------------|-------------------|
| Style | SATA |
| Cable Types | SATA |
| INPUT | |
| Cable Length (ft.) | 1.5 |
| Cable Length (in.) | 18 |
| PHYSICAL | |
| Color | Red |
| CONNECTIONS | |
| Connector A | 7 PIN SATA (MALE) |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|-------------------------------------|---------------------------|
| Connector B | 7 PIN ESATA (MALE) |
| Number of Connectors | 2 |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.