

## 1.44kW Single-Phase Metered PDU + Isobar Surge Suppression, 3840 Joules, 120V Outlets (14 5-15R), 5-15P, 15ft Cord, 1U Rack-Mount

MODEL NUMBER: **PDUMH15-ISO**



### Description

Tripp Lite Metered PDU / Power Distribution Unit with Isobar Surge Suppression offers real-time local reporting of load level in amps, plus premium ISOBAR network-grade AC surge and noise suppression. Digital display continuously reports PDU output current to prevent circuit overloads as additional equipment is added. Set of 3 front-panel LEDs provide notification of wiring fault, protection present and line OK status. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

### Features

- 15A single phase 120V Metered Power Distribution Unit / PDU (Agency de-rated to 12A continuous)
- Built-in 2 digit visual meter continuously reports PDU load level in amps
- ISOBAR Network-grade AC surge and noise suppression with 3840 Joules AC suppression rating and EMI/RFI filtering
- Set of 3 diagnostic LEDs report LINE OK (green), suppressor or wiring FAULT (red) and PROTECTION PRESENT (green) status
- Compatible with 120V AC sine wave input; For best results, connect the PDU only to true sine wave mains, generator or UPS power source (avoid connecting this surge suppressor to UPS systems producing modified sine wave, PWM sine wave and other non-sinusoidal output waveforms)
- Attached NEMA 5-15P 15A 120V input plug with 15ft / 4.5m cord
- 1U Horizontal rackmount format installs in one rack space
- Switchless design prevents accidental shut-off
- 14 NEMA 5-15R outlets (2 front / 12 rear)
- Included mounting accessories support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Back panel grounding lug

### Highlights

- Metered single phase 15A 120V PDU with Isobar Surge Suppression
- 1U Horizontal rackmount, Digital current meter
- 3840 Joule suppression rating, Diagnostic LEDs
- NEMA 5-15P input; 15ft / 4.5m line cord
- 14 NEMA 5-15R outlets (2 front / 12 rear)
- Reversible housing; 4.5in / 11.4cm depth

### Applications

- Ideal for a wide variety of Datacenter, Computer, IT and other rackmount applications

### Package Includes

- PDUMH15-ISO Metered PDU with Surge Suppression
- Owner's manual with warranty information

## Specifications



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Style	Rackmount, Vertical Rackmount, Wallmount/Under-Counter
PDU Type	Metered
<b>OUTPUT</b>	
Output Capacity Details	1.44kW (120V), 1.52kW (127V), 1.2kW (100V); 15A maximum (Agency de-rated to 12A continuous)
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(14) 5-15R
Output Nominal Voltage	100-127V nominal, single phase
Overload Protection	15A Breaker
Outlet Type	NEMA 5-15R
<b>INPUT</b>	
PDU Input Voltage	100; 120; 127
Recommended Electrical Service	15A 120V; For best results, connect the PDU only to true sine wave mains, generator or UPS power source (avoid connecting to UPS systems producing modified sine wave, PWM sine wave and other non-sinusoidal waveforms)
Maximum Input Amps	15
Maximum Input Amps Details	Agency de-rated to 12A continuous
PDU Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Input Phase	Single-Phase
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Two digit current meter reports PDU output load in amps
Front Panel LEDs	Set of 3 diagnostic LEDs continuously report status for LINE OK (green), suppressor or wiring FAULT (red) and PROTECTION PRESENT (green)
Switches	No power switch
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	3840
AC Suppression Response Time	NM = 0 ns. CM = <1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	140
AC Suppression Surge Current Rating	60,000 amps
EMI / RFI Filtering	40-80 dB
Immunity	Conforms to IEEE 587 / ANSI C62.41



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

PHYSICAL	
Shipping Dimensions (hwd / in.)	2.25 x 20.5 x 10
Shipping Dimensions (hwd / cm)	5.72 x 52.07 x 25.4
Shipping Weight (lbs.)	5.2
Shipping Weight (kg)	2.36
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 4.5
Unit Dimensions (hwd / cm)	4.45 x 44.45 x 11.43
Unit Weight (lbs.)	4.6
Unit Weight (kg)	2.1
Material of Construction	Sheet Metal
Form Factors Supported	1U rackmount, 0U vertical rackmount, wall-mount, and under-counter installation
PDU Form Factor	Horizontal (1U, 2U, etc)
ENVIRONMENTAL	
Storage Temperature Range	+5F to +122F (-15 to 50C)
Relative Humidity	5-95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
SPECIAL FEATURES	
TVSS Grounding	Rear grounding lug
CERTIFICATIONS	
Certifications	Tested to UL1449 3rd Edition (USA) and CSA (Canada), RoHS Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.