

## 1.4kW Single-Phase Metered PDU, 120V Outlets (14 5-15R), 5-15P, 15ft Cord, 0U Vertical, 36 in.

MODEL NUMBER: PDUMV15-36



### Description

Tripp Lite single phase Metered PDU / Power Distribution Units offer real-time local reporting of load level in amps via built-in digital display. Enables visual monitoring of PDU load levels to prevent overloads as additional equipment is added. Offers reliable rackmount multi-outlet power distribution from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

### Features

- 15A single phase 120V Metered Power Distribution Unit / PDU (Agency de-rated to 12A continuous)
- Two-digit lighted meter reports combined total output current in amps
- Attached NEMA 5-15P 15A 120V input plug with 15ft / 4.5m line cord
- 0U 36in / 91cm vertical rackmount format installs using no rack spaces
- 14 NEMA 5-15R outlets
- Includes 15A circuit breaker and lighted power switch inside a transparent protective cover
- Toolless installation supported in button-mount compatible equipment racks
- Bolt-down installation brackets support installation in other racks and additional surfaces

## Specifications

OVERVIEW	
Style	Vertical Rackmount, Wallmount, Raceway, Workbench
PDU Type	Metered
OUTPUT	

### Highlights

- Metered single phase 15A 120V 0U 36in / 91cm vertical rackmount PDU
- Two-digit current meter reports output current in amps
- Attached 15ft / 4.5m cord with NEMA 5-15P input plug
- 14 NEMA 5-15R outlets
- Toolless button mount and bolt-down bracket installation hardware included

### Applications

- Ideal means of powering networking equipment in datacenters, computer rooms and network closets

### Package Includes

- Metered Vertical PDU
- Mounting hardware and spare mounting buttons
- Owner's manual with warranty information



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Output Capacity Details	1.4kW (120V input), 1.5kW (127V input), 1.2kW (100V input); 15A maximum (Agency de-rated to 12A continuous)
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(14) 5-15R
Output (VA)	1800
Output Nominal Voltage	100-127V nominal, single phase
Overload Protection	15A
Outlet Type	NEMA 5-15R
<b>INPUT</b>	
PDU Input Voltage	100; 120; 127
Maximum Input Amps	15
Maximum Input Amps Details	Agency de-rated to 12A continuous
PDU Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.6
Input Phase	Single-Phase
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LEDs	Digital LED current monitor display
Switches	Lighted on/off switch with integrated safety cover
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	2.21 x 38.93 x 5.56
Shipping Dimensions (hwd / cm)	5.6 x 98.9 x 14.1
Shipping Weight (lbs.)	3.79
Shipping Weight (kg)	1.7
Unit Dimensions (hwd / in.)	36 x 1.75 x 1.25
Unit Dimensions (hwd / cm)	91.4 x 4.45 x 3.2
Unit Weight (lbs.)	3.2
Unit Weight (kg)	1.5
Material of Construction	Aluminum
Form Factors Supported	Vertical (0U) mounting in rack enclosures, horizontal mount in raceways and a variety of other applications
PDU Form Factor	Vertical (0U)
<b>ENVIRONMENTAL</b>	
Relative Humidity	5-95% non-condensing



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Operating Elevation (ft.)	0 to 3000M (0 to 10,000 Ft.)
<b>CERTIFICATIONS</b>	
Certifications	Tested to UL60950-1 (USA) and CSA60950-1 (Canada), NOM (Mexico), Class A (Emissions), RoHS Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.