

Power It! 4-Outlet Power Strip, 10-ft. Cord with ABS Fire Retardant Plastic Casing

MODEL NUMBER: PS410



Description

Tripp Lite's Power It! PS410 power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. Includes 4 NEMA 5-15R outlets, 10-foot AC power cord.. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features ABS fire retardant plastic case to stand up to the most demanding environments, illuminated power switch and 15A integrated circuit breaker to prevent dangerous overloads.

INPUT/OUTPUT: Input: NEMA 5-15P/Output: 4 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: Corded power distribution strip

Features

- Multi-outlet power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment
- Includes 4 NEMA 5-15R outlets
- Illuminated on/off switch provides one-touch power control for connected equipment
- 15A power handling capacity with integrated circuit breaker
- 120V AC, 50/60Hz electrical compatibility
- 10-foot AC power cord
- ABS fire retardant plastic case provides extra safety and durability
- UL certification

Highlights

- 4 outlets
- Illuminated on/off switch with cover
- 15-amp circuit breaker
- 10 ft. power cord
- ABS fire retardant plastic

Applications

- Offers a reliable, convenient and cost-effective method of power distribution for appliances, power tools, lighting and other electrical equipment in home, office or worksite.
- Unfiltered electrical pass-through makes the power strip ideal for distributing alternate waveform UPS or generator power to connected equipment.

Package Includes

- PS410 power strip
- Warranty information
- Instruction manual

Specifications

OVERVIEW

| | |
|-------|-------|
| Style | Strip |
|-------|-------|



| OUTPUT | |
|--|---|
| Frequency Compatibility | 50 / 60 Hz |
| Output Receptacles | (4) 5-15R |
| Output (Watts) | 1800 |
| Circuit Breaker (amps) | 15 |
| Overload Protection | 15A circuit breaker |
| Outlet Orientation | Single row of 4 |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 15A 120V |
| Input Connection Type | NEMA 5-15P |
| Input Cord Length (ft.) | 10 |
| Input Cord Length (m) | 1.8 |
| Input Cord Gauge Type | SJT 14AWG |
| Voltage Compatibility (VAC) | 120 |
| USER INTERFACE, ALERTS & CONTROLS | |
| Switches | Illuminated on/off switch controls power to all outlets |
| PHYSICAL | |
| Shipping Dimensions (hwd / in.) | 12 x 5.8 x 1.8 |
| Shipping Dimensions (hwd / cm) | 30.5 x 14.7 x 4.6 |
| Shipping Weight (lbs.) | 1.2 |
| Shipping Weight (kg) | .544 |
| Unit Dimensions (hwd / in.) | 1.2 x 1.85 x 8.1 |
| Unit Dimensions (hwd / cm) | 3 x 4.7 x 20.6 |
| Unit Weight (lbs.) | 1.4 |
| Unit Weight (kg) | .6 |
| Material of Construction | ABS Fire Retardant Plastic |
| Integrated Keyhole Mounting Tabs | Keyhole Slots |
| Receptacle Color | Light Gray |
| Color (AC Line Cord) | Light Gray |
| CERTIFICATIONS | |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|-------------------------------------|--|
| Additional International Approvals | Complies with RoHS (Restriction of Hazardous Substances Directive) |
| UL1363 (Power Tap) | UL1363 |
| cUL / CSA (Canada) | cUL |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.