

Power It! 7-Outlet Power Strip, 12-ft Cord, Diagnostic LED, Black Housing

MODEL NUMBER: **PS712B**



Description

Tripp Lite's PS712B power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. PS712B offers 7 total outlets, 12 foot cord. Attractive black housing with keyhole mounting slots and 1 designated transformer plug outlet. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket.

PLUG/OUTLETS: Input: NEMA5-15P/Output: 7 NEMA5-15R/12 ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with 1 transformer spaced outlet

Features

- 7 outlets / 12-ft cord
- Attractive black housing
- EMI/RFI noise filtering
- Can accommodate 1 transformer without blocking remaining outlets
- Diagnostic LEDs indicate protection present & ground present
- Keyhole supports for wall mounting

Specifications

| OVERVIEW | |
|-------------------------|------------|
| Style | Strip |
| OUTPUT | |
| Frequency Compatibility | 50 / 60 Hz |

Highlights

- 7 outlets
- 12 ft power cord
- Illuminated on/off switch
- 15 amp circuit breaker
- Keyhold mounting slots

Applications

- Offers a reliable convenient and cost-effective method of power distribution for appliances, power tools, lighting and other electrical equipment in home, office or worksite.

Package Includes

- PS712B Surge Suppressor
- Instruction manual and warranty information



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|--|
| Output Receptacles | (7) 5-15R |
| Output (Watts) | 1800 |
| Circuit Breaker (amps) | 15 |
| Transformer Accommodation | Supports 1 large transformer plug accessory without covering remaining outlets, accepts up to 4 transformers total |
| Outlet Orientation | Single row |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 120V (110-125V) |
| Input Connection Type | NEMA 5-15P |
| Input Cord Length (ft.) | 12 |
| Input Cord Length (m) | 3.66 |
| Input Cord Gauge Type | 14 gauge, SJT |
| Voltage Compatibility (VAC) | 120 |
| Maximum Surge Amps | 72000 |
| USER INTERFACE, ALERTS & CONTROLS | |
| Switches | Combination AC circuit breaker and 2 position red illuminated on/off power switch |
| DATALINE SURGE SUPPRESSION | |
| Cable (Coax) Protection | No |
| Network (Ethernet) Protection | No |
| PHYSICAL | |
| Shipping Dimensions (hwd / in.) | 13.78 x 4.92 x 2.36 |
| Shipping Dimensions (hwd / cm) | 35.00 x 12.50 x 5.99 |
| Shipping Weight (lbs.) | 1.92 |
| Shipping Weight (kg) | 0.87 |
| Unit Dimensions (hwd / in.) | 1.32 x 2.05 x 11.69 |
| Unit Dimensions (hwd / cm) | 3.35 x 5.21 x 29.69 |
| Unit Weight (lbs.) | 1.76 |
| Unit Weight (kg) | 0.80 |
| Material of Construction | Plastic |
| Integrated Keyhole Mounting Tabs | Keyhole mounting slots enable wall mounting |
| Receptacle Color | Black |
| Color (AC Line Cord) | Black |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|---|
| Outlets Measurement (Center to Center) | Distance between standard outlets = 29mm; Distance between last standard outlet and transformer outlet = 33mm |
| Keyhole Slot Mounting Measurement (Center to Center) | Distance between slots = 151mm; Distance between slot height = 24mm |
| CERTIFICATIONS | |
| Additional International Approvals | RoHS |
| NOM (Mexico) | NOM |
| UL1363 (Power Tap) | UL1363 |
| cUL / CSA (Canada) | cUL |
| Approvals | Exceeds IEEE 587 category A&B specifications |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.