

www.tripplite.com

# Internal SAS Cable, mini-SAS (SFF-8087) to mini-SAS (SFF-8087), 18-in. (0.5M)

## MODEL NUMBER: \$506-18N



### Highlights

- Positive and passive latching ensures that the plug remains mated to receptacle
- All internal Mini-SAS assemblies are capable of supporting SAS/SATA generation I, II, and III bandwidths ( up to 6Gbps )
- Reduced mechanical size offers up to 4 times the port density of the current x4 solution

#### Package Includes

• 18inch Internal SAS Cable, SFF-8087 to SFF-8087

#### Description

Internal Mini-SAS Double-Ended Plug with Sidebands, SFF-8087 to SFF-8087, 36 Circuits, 30 AWG, 18 in. length, controller to backplane.

#### Features

- Positive and passive latching ensures that the plug remains mated to receptacle
- All internal mini SAS assemblies are capable of supporting SAS/SATA generation I, II, and III bandwidths (up to 6Gbps)
- Reduced mechanical size offers up to 4 times the port density of the current x4 solution
- For Controller to Backplane applications

# Specifications

OVERVIEW	
Style	SCSI
Model Type	Internal
Cable Types	SAS
INPUT	
Cable Length (ft.)	1.5
Cable Length (in.)	18
PHYSICAL	
Color	Black



CONNECTIONS		
Connector A	SFF-8087	
Connector B	SFF-8087	
Number of Connectors	2	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.