

Internal SAS Cable, mini-SAS (SFF-8087) to 4-in-1 32pin (SFF-8484), 3-ft (1M).

MODEL NUMBER: **S510-003**



Highlights

- Positive and passive latching ensures that the plug remains mated to receptacle
- All internal Mini-SAS assemblies are capable of supporting SAS/SATA generation I, II, and III bandwidths (up to 6Gbps)
- Reduced mechanical size offers up to 4 times the port density of the current x4 solution

Package Includes

- 3ft Internal SAS Cable, Mini-SAS SFF-8087 to SFF-8484

Description

3 ft. Internal Mini-SAS SFF-8087 to SFF-8484 controller to backplane cable. 30AWG, 8-pair cable with sideband signaling.

Features

- Positive and passive latching ensures that the plug remains mated to receptacle
- All internal iPass assemblies are capable of supporting SAS/SATA generation I, II, and III bandwidths (up to 6Gbps)
- Reduced mechanical size offers up to 4 times the port density of the current x4 solution
- For Controller to Backplane applications

Specifications

OVERVIEW	
Style	SCSI
Model Type	Internal
Cable Types	SAS
INPUT	
Cable Length (ft.)	3
Cable Length (m)	0.91
PHYSICAL	
Color	Gray



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Connector A	SFF-8087
Connector B	SFF-8484
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.