

External SAS Cable, 4 Lane - mini-SAS (SFF-8088) to mini-SAS (SFF-8088), 2M (6-ft.)

MODEL NUMBER: **S524-02M**



Highlights

- High-performance 2-meter SAS external cable
- Mini-SAS SFF-8088 (iSAS) to Mini-SAS SFF-8088 (iSAS)

System Requirements

- SAS Controllers, SAS Chassis, SAS/SATA Hard Drives

Package Includes

2-Meter SAS External, SFF-8088 to SFF-8088 Cable

Description

Tripp Lite's S524-02M External SAS cable features SFF-8088 to SFF-8088 "mini-SAS" connectors with heavy-duty metal backshells. This 4-channel Infiniband cable is constructed with high-performance cable, which features individually shielded parallel pairs, double EMI/RFI shielding, and 6.0 Gigabytes per second performance.

Features

- 2-meter External SAS Cable, SFF-8088 to SFF-8088
- Made with High-Performance Infiniband Cable
- Support data rates from 3.0 up to 6.0 gigabytes per second
- SFF-8088 connectors in diecast zinc housing for durability
- RoHS compliant

Specifications

OVERVIEW	
Style	Serial Attached SCSI (SAS)
Model Type	External
Cable Types	SAS
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.83
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color	Black
CONNECTIONS	
Connector A	SFF-8088
Connector B	SFF-8088
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.