

Protect It! 3-Outlet Surge Protector, Direct Plug-In, 540 Joules, 2.1 A USB Charger, Diagnostic LED

MODEL NUMBER: SK30USB



Highlights

- 3 outlets/direct plug-in
- 540 joule rating
- 2.1 amp USB charging
- Diagnostic LED
- \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

- Ideal for any desktop, network or home computing application requiring AC protection
- Dual port USB charging ports for smartphones, tablets, MP3 Players and other portable devices

Package Includes

- SK30USB surge suppressor

Description

The SK30USB surge suppressor offers reliable surge and line noise protection. The compact direct plug-in design allows for easy portability and features 3 outlets and 540 joules of surge energy absorption. Diagnostic LED alerts you to potential wiring or protection faults before connected equipment is damaged. 2.1 amp USB charging ports offer fast charging for smartphones, tablets, MP3 players and other portable devices. \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 3 outlets / direct plug-in
- Surge suppression rating: 540 joules
- 2.1 amp USB Charger
- EMI/RFI noise filtering
- Diagnostic LED indicates Protected (green)
- \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW	
Style	Direct Plug-In
OUTPUT	
Charging Ports / Amps	(2) 2.1A
Frequency Compatibility	60 Hz
Output Receptacles	(3) 5-15R
Output (Watts)	1800



Circuit Breaker (amps)	15
Outlet Type	NEMA 5-15R
USB Charging	Yes
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Connection Type	NEMA 5-15P input plug
Input Plug Features	120V, 15A
Input Cord Length (ft.)	0
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	540
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
Clamping Voltage (RMS)	500
AC Suppression Surge Current Rating	27,000
UL1449 Let Through Rating	500, 400, 500
Immunity	Conforms to IEE 587/ANSI C62.41
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Direct plug-in suppressor mounts directly to a wall receptacle
Housing Color	Black
Receptacle Color	Black
SPECIAL FEATURES	
Right-Angle Plug	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$5,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.