

48U Heavy-Duty 4-Post SmartRack Open Frame Rack - Organize and Secure Network Rack Equipment

MODEL NUMBER: SR4POST48HD











Highlights

- 48U Heavy-Duty 4-post open frame rack
- Black steel with square, numbered mounting holes
- Toolless button holes to accept
 PDUs or cable managers

Package Includes

- SR4POST48HD Heavy-Duty
 4-Post Open Frame Rack
- · Installation hardware
- (2x) PDU/Cable management brackets
- Owner's manual with warranty information

Description

SmartRack 4-post heavy-duty open frame racks are an economical solution for 19-inch rackmount applications.

Features

- Weight capacity of 3000 lbs. stationary
- Supports equipment depths up to 35 inches
- Textured, black powder coat finish
- Heavy-duty cold-rolled steel construction
- · Numbered mounting positions
- Bolt down provisions
- · Self-squaring design
- Easy assembly
- $\bullet \ \ \text{Optional SRCASTERHDKIT heavy-duty caster kit permits mobile use of 3,000 lb rolling loads}$
- Optional SR48SIDE4PHD side panels for end-of-the-row aesthetics

Specifications

OVERVIEW	
Style	4-Post
PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	35.25





Installed Whole System Maximum Rack Depth (cm)	89.54	
Rack Height (U Spaces)	48	
Shipping Dimensions (hwd / in.)	6.75 x 9.5 x 93.75	
Shipping Dimensions (hwd / cm)	17.15 x 24.13 x 238.13	
Shipping Weight (lbs.)	117	
Shipping Weight (kg)	52.65	
Unit Dimensions (hwd / in.)	90 x 24 x 35.25	
Unit Weight (lbs.)	110	
Unit Weight (kg)	49.5	
Unit Dimensions (cm)	279.4 x 60.96 x 89.54	
Color	Black	
Weight Capacity - Stationary (lbs.)	3000	
Weight Capacity - Stationary (kg)	1350	
Hinged (Swings Away from Wall Bracket)	No	
CERTIFICATIONS		
NOM (Mexico)	Tested to NOM (Mexico)	
Approvals	EIA-310-D, IEC 60297-3-100, DIN 41494, RoHS	
WARRANTY		
Product Warranty Period (Worldwide)	5-year limited warranty	
	·	

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.