

SmartRack Wall-Mount Roof Fan Kit - 2-120V high-performance fans; 210 CFM; 5-15P plug

MODEL NUMBER: **SRFANWM**



Highlights

- Wall-Mount Roof Fan Kit - 120V
- Features (2) 120V high-performance fans, 3-ft. cord
- 50 dB sound rating

Applications

Ideal use for increased airflow in wall-mount enclosure applications.

Package Includes

- (2) 120V high-performance fans with 3 foot power cord
- (2) Fan guards
- Mounting hardware
- Owner's manual

Description

Tripp Lite's SmartRack Wall-Mount Roof Fan Kits are the ideal solution for increasing ventilation in wall-mount enclosure cabinets. Each kit features multiple high-performance fans that can be installed to the inside or outside of the wall-mount enclosure to expel heat out of the enclosure.

COMPATIBLE SMARTTRACK WALL-MOUNT ENCLOSURES - SRW6U, SRW9U, SRW10US, SR12UB, SRW12U, SRW12US, SRW12US33, SRW12USG, SRW18US, SRW26US, and other Tripp Lite SmartRack Enclosures that specify the use of this accessory.

Features

- (2) 120V High-Performance Fans (210 CFM total)
- 50 dB sound rating
- 3-foot AC input cord with 5-15P input plug

Specifications

OVERVIEW	
Model Type	Passive Cooling
Accessories Type	Fan Kit
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Nominal Input Voltage Description	120V 50/60 Hz
Input Plug Features	NEMA 5-15P
Input Cord Length (ft.)	3
Input Cord Length (m)	0.9



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Shipping Dimensions (hwd / in.)	2.5 x 7.25 x 11.5
Shipping Dimensions (hwd / cm)	6.35 x 18.4 x 29.2
Shipping Weight (lbs.)	3.8
Shipping Weight (kg)	1.71
Unit Dimensions (hwd / in.)	5.20 x 5.20 x 1.61
Unit Dimensions (hwd / cm)	Per Fan 13.21 x 13.21 x 4.1
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.