

SmartRack 12U Wall-Mount Open Frame Rack

MODEL NUMBER: SRWO12UHD



Highlights

- Open frame with 2 post mounting, 19" Width, 18" Depth
- Threaded (12-24) mounting holes
- Heavy duty steel frame
- Easy assembly

Package Includes

- (1) 3mm L-Shaped Hex Key
- (2) Top/Bottom Panel Frames
- (2) Vertical Mounting Rails
- (8) M5 Button Head Cap Screws
- (24) #12-24 Equipment Mounting Screws

Description

Designed with provisions to integrate wall mounting, easy equipment access and cable management, SmartRack wall-mounted open frame cabinets are perfect for network equipment in IT environments with limited floor space. The 19" wide open frame rack is a heavy-duty, open frame rack designed for secure, high density servers and networking applications in IT environments.

Features

- 2-post wall mounting...EIA 19" width
- Threaded (12-24) mounting holes
- Heavy duty steel construction with diagonal support straps
- Durable black textured powder coat finish
- Easy Assembly

Specifications

OVERVIEW	
Style	Wall Mounted
PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	18
Installed Whole System Maximum Rack Depth (cm)	45.72
Rack Height (U Spaces)	12
Shipping Dimensions (hwd / in.)	4 x 22 x 23.8
Shipping Dimensions (hwd / cm)	10.16 x 55.88 x 60.45



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (lbs.)	15.4
Shipping Weight (kg)	6.98
Unit Dimensions (hwd / in.)	24.8 x 20.1 x 18.24
Unit Weight (lbs.)	14.3
Unit Weight (kg)	6.48
Unit Dimensions (cm)	EXTERNAL DIMENSIONS: 63 x 51 x 46.3(HWD)
Color	Black
Weight Capacity - Stationary (lbs.)	200
Weight Capacity - Stationary (kg)	90.718
Hinged (Swings Away from Wall Bracket)	No
CERTIFICATIONS	
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA-310-D, IEC 60297-3-100, DIN 41494, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.