

3 Breaker Maintenance Bypass Panel for SU20K3/3, SU20K3/3XR5, SU20K3/3X and SU20KX UPS

MODEL NUMBER: **SU20KMBPK**



Highlights

- Wallmount manual bypass panel isolates UPS from connected loads for maintenance with no loss of network availability
- Includes Kirk-Key interlock system enhances system reliability
- 3 built-in circuit breakers, heavy duty buswork
- Compatible with select Tripp Lite 3 phase UPS systems

Description

Wallmount 3 breaker manual bypass panel with Kirk Key interlock system isolates the UPS from connected loads for maintenance with no loss of network availability. 70A breaker with KAIC rating of 14/18. Key included.

Compatible with Tripp Lite SU20K3/3, SU20K3/3XR5, SU20K3/3X, SU20KX

Features

- Wallmount 3 breaker manual bypass panel with Kirk Key interlock system
- Isolates the UPS from connected loads for maintenance with no loss of network availability
- 70A breaker with KAIC rating of 14/18
- Key included
- Compatible with Tripp Lite SU20K3/3, SU20K3/3XR5, SU20K3/3X, SU20KX

Specifications

OVERVIEW	
Model Type	Bypass Panels
Accessories Type	Bypass Panel
INPUT	
Nominal Input Voltage(s) Supported	240V AC; 415V AC
Voltage Compatibility (VAC)	240; 415
PHYSICAL	
Shipping Dimensions (hwd / in.)	38.2 x 24.87 x 9.75



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / cm)	97 x 63.2 x 24.8
Shipping Weight (lbs.)	130
Shipping Weight (kg)	59
Unit Dimensions (hwd / in.)	37.36 x 24.12 x 9
Unit Dimensions (hwd / cm)	94.9 x 61.3 x 22.9
Unit Weight (lbs.)	125
Unit Weight (kg)	56.75
Form Factors Supported	Wallmount
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.