

3 Breaker Maintenance Bypass Panel for SU60KX, SU60KTV

MODEL NUMBER: **SU60KMBPKX**



Highlights

- Wallmount manual bypass panel isolates UPS from connected loads for maintenance with no loss of network availability
- Includes Kirk-Key interlock system enhances system reliability
- 3 built-in circuit breakers, heavy duty buswork
- Compatible with select Tripp Lite 3 phase UPS systems

Description

Wallmount 3 breaker manual bypass panel with Kirk Key interlock system isolates the UPS from connected loads for maintenance with no loss of network availability. 125A breaker with KAIC rating of 35. Key included.

Compatible with Tripp Lite SU60KX, SU60KTV

Features

- Wallmount 3 breaker manual bypass panel with Kirk Key interlock system
- Isolates the UPS from connected loads for maintenance with no loss of network availability
- 125A breaker with KAIC rating of 35
- Key included
- Compatible with Tripp Lite SU60KX, SU60KTV

Specifications

OVERVIEW	
Model Type	Bypass Panels
Accessories Type	Bypass Panel
INPUT	
Nominal Input Voltage(s) Supported	480V AC
Voltage Compatibility (VAC)	480
PHYSICAL	
Shipping Dimensions (hwd / in.)	43.2 x 30.87 x 12.5



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / cm)	109.7 x 78.4 x 31.8
Shipping Weight (lbs.)	225
Shipping Weight (kg)	102
Unit Dimensions (hwd / in.)	42.36 x 30.12 x 11.75
Unit Dimensions (hwd / cm)	107.6 x 76.5 x 29.8
Unit Weight (lbs.)	220
Unit Weight (kg)	99.9
Form Factors Supported	Wallmount
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.