

3-Breaker Parallel Tie Cabinet with Maintenance Bypass Switch (for SU40K 3-Phase UPS)

MODEL NUMBER: **SUPC2MBP40K**



Highlights

- 3 breaker parallel tie cabinet accessory for two Tripp Lite 40kVA 3 phase UPS systems
- Links the output of two UPS systems for 80kVA non-redundant operation
- Integral Maintenance Bypass switch enables UPS maintenance or replacement
- 3 built-in circuit breakers, heavy duty copper buswork
- Compatible Tripp Lite SU40K 3 phase UPS systems

Description

Tripp Lite's parallel tie cabinet provides a means for safely paralleling two UPS systems for non-redundant combined mode operation. Non-redundant configuration combines the output of two UPS systems to support twice the output current. Built-in Maintenance Bypass Switch enables UPS maintenance and repair of with no disruption in power to connected equipment. Two input breakers receive incoming power from the UPS and are connected to heavy duty copper buswork and an output breaker rated for the total UPS capacity of the two UPS systems combined. See owners manual and [Tripp Lite Parallel Tie Cabinet with Bypass Panel](#) download for detailed specifications, dimensional drawings, operational flow charts and technical descriptions.

Compatible with two Tripp Lite SU40K UPS systems.

Features

- Tripp Lite's parallel tie cabinet provides a means for safely paralleling two UPS systems for non-redundant combined mode operation
- Non-redundant configuration combines the output of two UPS systems to support twice the output current
- Built-in Maintenance Bypass Switch enables UPS maintenance and repair of with no disruption in power to connected equipment
- Two input breakers receive incoming power from the UPS and are connected to heavy duty copper buswork and an output breaker rated for the total UPS capacity of the two UPS systems combined
- Compatible with two Tripp Lite SU40K UPS systems

Specifications

OVERVIEW	
Model Type	Tie Cabinets
Accessories Type	Parallel Tie Cabinet
INPUT	
Nominal Input Voltage(s) Supported	208V AC



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Voltage Compatibility (VAC)	208
PHYSICAL	
Shipping Dimensions (hwd / in.)	62 x 36.88 x 12.5
Shipping Dimensions (hwd / cm)	157.5 x 98.8 x 31.75
Shipping Weight (lbs.)	375
Shipping Weight (kg)	170.3
Unit Dimensions (hwd / in.)	61.25 x 36.12 x 11.8
Unit Dimensions (hwd / cm)	155.6 x 91.7 x 29.8
Unit Weight (lbs.)	370
Unit Weight (kg)	168
Form Factors Supported	Wallmount
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.