

240V Corded UPS Backplate Outlet Kit for SU6000RT3U and SU6000RT3UXR, L6-30R, L6-20R, 5-15/20R

MODEL NUMBER: **SUPDM13**



Description

Tripp Lite's SUPDM13 corded backplate kit converts Tripp Lite's hardwire SU6000RT3U or SU6000RT3UXR UPS system into one with AC plug and outlets. 10 ft./3m input line cord with L6-30P plug enables simple connection to 240V 30A mains power. Includes 1 L6-30R, 2 L6-20R and 10 5-15/20R output receptacles. Easy quick-connect wiring installs in minutes.

VOLTAGE COMPATIBILITY NOTE - SUPDM13 supports SU6000RT3U and SU6000RT3UXR applications configured for 240V nominal input voltage only (See SUPDM12 for 208V input voltage configurations).

Features

- Converts Tripp Lite's hardwire SU6000RT3U or SU6000RT3UXR UPS system to one with an AC plug and outlets
- 10 ft./3m AC line cord with L6-30P input plug-in connection
- Includes 1 L6-30R, 2 L6-20R and 10 5-15/20R output receptacles
- Easy quick-connect wiring installs in minutes

Specifications

OVERVIEW	
Model Type	Outlet Kits
Accessories Type	Backplate Outlet Kit
OUTPUT	
Output Receptacles	(10) 5-15/20R; (2) L6-20R; (1) L6-30R
Output Nominal Voltage	Simultaneous 240 and 120V output

Highlights

- Converts Tripp Lite's hardwire SU6000RT3U UPS systems to one with AC plug and outlets
- For use with 240V UPS output voltage configurations
- 10 ft. / 3m AC input power cable with NEMA L6-30P input plug
- 1 L6-30R, 2 L6-20R and 10 5-15/20R output receptacles
- Easy quick-connect wiring installs in minutes

Applications

- Ideal for 240V applications calling for Tripp Lite's SU6000RT3U and SU6000RT3UXR UPS systems where plug-in AC input and output connections are required



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Overload Protection	120V outlets are protected by 2 separate 20A branch rated circuit breakers
INPUT	
Nominal Input Voltage(s) Supported	208V AC
UPS Input Cord Length (ft.)	10 ft. / 3m
UPS Input Cord Length (m)	3.05
Recommended Electrical Service	30A 240V
Input Connection Type	NEMA L6-30P input plug
Voltage Compatibility (VAC)	208
PHYSICAL	
Shipping Dimensions (hwd / in.)	5.5 x 9 x 14.25
Shipping Dimensions (hwd / cm)	14 x 22.9 x 36.2
Shipping Weight (lbs.)	6.6
Shipping Weight (kg)	3
Unit Dimensions (hwd / in.)	2.5 x 5 x 11
Unit Dimensions (hwd / cm)	6.4 x 12.7 x 28
Unit Weight (lbs.)	6
Unit Weight (kg)	2.8
Material of Construction	Steel
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.