

SUPDM710HW - UPS Accessory - Hardwire PDU Module

MODEL NUMBER: **SUPDM710HW**



Description

The SUPDM710HW converts the output of Tripp Lite SmartOnline SU8000RT3U and SU10000RT3U to a totally hardwired solution. Easy quick-connect terminal blocks allow installation in minutes. Can accept input voltages of 200-240 VAC. Hardwire input/output connections.

Features

- Converts the output of Tripp Lite SmartOnline SU8000RT3U and SU10000RT3U to a totally hardwired solution
- Easy quick-connect terminal blocks allow installation in minutes
- Can accept input voltages of 200-240 VAC
- Hardwire input/output connections

Specifications

OVERVIEW	
Model Type	PDU Modules
Accessories Type	PDU Module
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	Hardwire
Output Nominal Voltage	200-240v
INPUT	
Nominal Input Voltage(s) Supported	208V AC; 240V AC
Input Connection Type	Hardwire

Highlights

- Converts compatible SmartOnline high-voltage UPS systems to a totally hardwired solution
- For use with SU10000RT3U and SU8000RT3U UPS Systems
- Hardwired input/output connections
- Easy quick-connect terminal block installation

Applications

- Use with Tripp Lite SU10000RT3U and SU8000RT3U UPS systems in 200-240 applications where hardwire input/output connections are required

System Requirements

- Use with SU10000RT3U and SU8000RT3U SmartOnline UPS Systems

Package Includes

- Hardwire PDU
- Mounting Hardware
- Owner's Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Voltage Compatibility (VAC)	208; 240
PHYSICAL	
Shipping Dimensions (hwd / in.)	9.75 x 8.5 x 7.75
Shipping Dimensions (hwd / cm)	24.8 x 21.6 x 19.7
Shipping Weight (lbs.)	4.8
Shipping Weight (kg)	2.2
Unit Dimensions (hwd / in.)	5.25 x 7.5 x 5.25
Unit Dimensions (hwd / cm)	13.3 x 19.1 x 13.3
Unit Weight (lbs.)	3.8
Unit Weight (kg)	1.7
Material of Construction	Steel
CERTIFICATIONS	
Certifications	Tested to UL1778 (USA), CSA (Canada), RoHS compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.