

Detachable redundant PDU option for select SmartOnline UPS - Hardwired input / L6-20R, L6-30R output

MODEL NUMBER: **SUPDMB20K8**



Description

SUPDMB20K8 combines the output of two compatible SU8000RT3UPM or SU10000RT3UPM UPS power modules for fault-tolerant N+1 or increased capacity configurations. Manual bypass feature enables hot-swappable replacement of both power modules with no disruption in power to connected equipment.

(IMPORTANT > compatible only with SU8000RT3UPM and SU10000RT3UPM power modules built after 6/2010 with built-in USB and PARALLEL back panel data connections).

Features

Specifications

OVERVIEW	
Model Type	PDU Modules; Outlet Kits
Accessories Type	PDU Module
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) L6-20R; (2) L6-30R
Output Nominal Voltage	200-240VAC
Overload Protection	8 double pole 20A breakers, 2 double pole 30A breakers

Highlights

- Converts compatible SmartOnline 8 and 10kVA high-voltage UPS configurations for N+1 redundancy or increased capacity when used along with a 2nd compatible UPS power module
- Manual bypass feature enables hot-swappable replacement of both power modules while connected equipment runs uninterrupted
- Hardwired input / L6-20R & L6-30R outlets

Applications

- Ideal for use as a replacement redundant bypass PDU or means of enabling N+1 or increased capacity for configurations involving two compatible UPS power modules

System Requirements

- For use only with configurations involving two compatible SU8000RT3UPM or SU10000RT3UPM power modules (requires two of the same model power module built after 6/2010 originally shipping with built-in USB and PARALLEL back panel data connections)

Package Includes

- SUPDMB20K8 parallel PDU
- Parallel cable
- Owner's Manual



INPUT	
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 230V AC; 240V AC; 220V AC
Input Connection Type	Hardwire
Voltage Compatibility (VAC)	200; 208; 230; 240; 220
PHYSICAL	
Shipping Dimensions (hwd / in.)	10 x 23.9 x 12.1
Shipping Dimensions (hwd / cm)	25.4 x 60.7 x 30.7
Shipping Weight (lbs.)	14.52
Shipping Weight (kg)	6.6
Unit Dimensions (hwd / in.)	20.5 x 7 x 4.5
Unit Dimensions (hwd / cm)	52.1 x 17.8 x 11.4
Unit Weight (lbs.)	14.52
Unit Weight (kg)	6.6
Material of Construction	Sheet metal
CERTIFICATIONS	
Certifications	Tested to UL1778 4th Edition (USA), CSA (Canada), EN62040-1
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.