

## SUPDMB568HW - UPS Accessory - Hardwire PDU Module

MODEL NUMBER: **SUPDMB568HW**



### Description

The SUPDMB568HW hardwire input/output PDU module converts compatible SmartOnline Hot-Swappable Modular UPS Systems (models SU5000RT4U, SU6000RT4U, and SU8000RT4U) to a totally hardwired solution. Easy quick-connect terminal block allows installation of hardwire distribution module in minutes. Can accept input voltages of 120/208 or 120/240 VAC split-phase power. Detachable hardwire module with manual bypass switch allows for effortless UPS maintenance without the need to power down connected loads and re-wire input/output connections.

### Features

- Converts compatible SmartOnline Hot-Swappable Modular UPS Systems (models SU5000RT4U, SU6000RT4U, and SU8000RT4U) to a totally hardwired solution
- Easy quick-connect terminal block allows installation of hardwire distribution module in minutes
- Can accept input voltages of 120/208 or 120/240 VAC split-phase power
- Detachable hardwire module with manual bypass switch allows for effortless UPS maintenance without the need to power down connected loads and re-wire input/output connections

### Highlights

- Converts compatible SmartOnline Hot-Swappable Modular UPS systems to hardwire input and output
- For use with input voltages of 120/208 or 120/240 VAC split-phase power
- Convenient quick-disconnect terminal block allows installation in minutes
- Manual bypass switch eliminates equipment downtime

### Applications

- Use with Tripp Lite SU5000RT4U, SU6000RT4U, and SU8000RT4U UPS systems in 120, 208/240V applications where hardwire input/output connections are required

### System Requirements

- Use with SU5000RT4U, SU6000RT4U, and SU8000RT4U split-phase SmartOnline Hot-Swappable Modular UPS Systems

### Package Includes

- SUPDMB568HW hardwire PDU
- Mounting Hardware
- Owner's Manual

## Specifications

OVERVIEW	
Model Type	PDU Modules
Accessories Type	PDU Module
OUTPUT	
Frequency Compatibility	50 / 60 Hz



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Output Receptacles	Hardwire
Output Nominal Voltage	120/208, 120/240
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	100V AC; 110V AC; 115V AC; 120V AC; 127V AC; 140V AC
Input Connection Type	Split-phase hardwire (4-wire)
Voltage Compatibility (VAC)	100-140
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	9.5 x 20.5 x 9.75
Shipping Dimensions (hwd / cm)	24.1 x 52.1 x 24.8
Shipping Weight (lbs.)	14
Shipping Weight (kg)	6.3
Unit Dimensions (hwd / in.)	6 x 17.5 x 6.75
Unit Dimensions (hwd / cm)	15.24 x 44.45 x 17.1
Unit Weight (lbs.)	11.7
Unit Weight (kg)	5.3
Material of Construction	Steel
<b>CERTIFICATIONS</b>	
Certifications	Tested to UL1778 (USA), CSA (Canada), RoHS compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.