

## Detachable PDU option for compatible SmartOnline UPS Systems, Hardwired Input/Output

MODEL NUMBER: **SUPDMB6KHW**



### Description

The SUPDMB6KHW UPS backplate with manual transfer switch serves as a replacement for the original backplate provided with SU6000RT4UHVHW and SU6000RT4UTFHW configurations. Can also be used to convert any high voltage UPS configuration using the SU6000RT4UHVPM power module to support hardwire input and output. Manual bypass feature ensures maximum availability of connected equipment while UPS maintenance occurs. Can accept input voltages of 200-240 VAC. Hardwire input and output.

### Features

### Highlights

- Detachable PDU backplate with manual bypass switch serves as a replacement PDU for configured SU6000RT4UHVHW and SU6000RT4UTFHW UPS systems
- Can also be used to convert any high voltage UPS configuration using the SU6000RT4UHVPM power module to include hardwire output
- Hardwire input and output supported
- Attaches via unit-specific back panel electrical and bolt-on connections
- Manual bypass feature ensures maximum equipment availability

### System Requirements

- Requires SU6000RT4UHVPM UPS power module in any 200-240V AC configuration

### Package Includes

- SUPDMB6KHW detachable PDU

## Specifications

OVERVIEW	
Model Type	PDU Modules
Accessories Type	PDU Module
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	Hardwire
Output Nominal Voltage	200, 208, 220, 230, 240 VAC
INPUT	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Nominal Input Voltage(s) Supported	200V AC; 208V AC; 230V AC; 240V AC; 220V AC
Input Connection Type	Hardwire
Voltage Compatibility (VAC)	200; 208; 220; 230; 240
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	6.9 x 20.1 x 10.8
Shipping Dimensions (hwd / cm)	17.5 x 51.1 x 27.4
Shipping Weight (lbs.)	6.6
Shipping Weight (kg)	3
Unit Dimensions (hwd / in.)	3.3 x 17.2 x 3.2
Unit Dimensions (hwd / cm)	8.4 x 43.7 x 8.1
Unit Weight (lbs.)	7.7
Unit Weight (kg)	3.5
Material of Construction	Sheet metal
<b>CERTIFICATIONS</b>	
Certifications	Tested to UL1778 (USA), CSA (Canada), CE (EU)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.