

## Detachable PDU option for compatible SmartOnline UPS Systems, Hardwired Input/L6-20R and L6-30R

MODEL NUMBER: **SUPDMB710**



### Description

The SUPDMB710 converts the output of SmartOnline SU8000RT3U and SU10000RT3U power modules to North American L6-20R and L6-30R output connections. Manual bypass feature ensures maximum availability of connected equipment while UPS maintenance occurs. Can accept input voltages of 200-240 VAC. Hardwire input / 2 L6-30R and 4 L6-20R output connections.

### Features

- Converts compatible SmartOnline high-voltage UPS systems to provide North American 20 and 30A outputs
- For use with input voltages of 200-240 VAC
- Hardwired input / 2 L6-30R and 4 L6-20R output connections
- Manual bypass feature ensures maximum equipment availability

## Specifications

OVERVIEW	
Model Type	Outlet Kits
Accessories Type	PDU Module
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(4) L6-20R; (2) L6-30R
Output Nominal Voltage	208/240 VAC
Overload Protection	2 double pole 30A breakers, 2 double pole 20A breakers

### Highlights

- Converts compatible SmartOnline high-voltage UPS systems to provide North American 20 and 30A outputs
- For use with input voltages of 200-240 VAC
- Hardwired input / 2 L6-30R and 4 L6-20R output connections
- Manual bypass feature ensures maximum equipment availability

### Applications

- Ideal for use with Tripp Lite's SU8000RT3U and SU10000RT3U power modules in 200-240V applications where hardwire input / C19 output connections are required

### System Requirements

- For use with SmartOnline SU8000RT3U and SU10000RT3U Rack/Tower UPS systems in applications requiring a detachable PDU with manual bypass

### Package Includes

- SUPDMB710 detachable PDU
- Mounting hardware
- Owner's Manual with warranty instructions



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

INPUT	
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 230V AC; 240V AC; 220V AC
Input Connection Type	Hardwire
Voltage Compatibility (VAC)	200; 208; 220; 230; 240
PHYSICAL	
Shipping Dimensions (hwd / in.)	12.25 x 9.25 x 8.25
Shipping Dimensions (hwd / cm)	31.1 x 23.5 x 21
Shipping Weight (lbs.)	9.75
Shipping Weight (kg)	4.42
Unit Dimensions (hwd / in.)	10.25 x 7.5 x 6.5
Unit Dimensions (hwd / cm)	26 x 19.1 x 16.5
Unit Weight (lbs.)	8.75
Unit Weight (kg)	3.97
Material of Construction	Sheet metal
CERTIFICATIONS	
Certifications	Tested to UL1778 (USA), CSA (Canada)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.