

## SUPDMB710HW - UPS Accessory - Hardwire PDU Module

MODEL NUMBER: SUPDMB710HW



### Description

The SUPDMB710HW hardwire input/output PDU module converts compatible SmartOnline Hot-Swappable Modular UPS Systems (models SU10000RT3U and SU8000RT3U) to a totally hardwired solution. Easy quick-connect terminal block allows installation of hardwire distribution module in minutes. Can accept input voltages of 208 or 240 VAC single phase power. Detachable hardwire module with manual bypass switch allows for effortless UPS maintenance without the need to power down connected loads and re-wire input/output connections.

### Features

- Converts compatible SmartOnline Hot-Swappable Modular UPS Systems (models SU10000RT3U and SU8000RT3U) to a totally hardwired solution
- Easy quick-connect terminal block allows installation of hardwire distribution module in minutes
- Can accept input voltages of 208 or 240 VAC single phase power
- Detachable hardwire module with manual bypass switch allows for effortless UPS maintenance without the need to power down connected loads and re-wire input/output connections

### Highlights

- Converts compatible SmartOnline Hot-Swappable Modular UPS systems to hardwire input and output
- For use with SU10000RT3U and SU8000RT3U UPS Systems
- Easy quick-connect terminal block installation
- Manual bypass switch supports hot-swap UPS power module replacement

### Applications

- Use with Tripp Lite SU10000RT3U and SU8000RT3U UPS systems in 208/240V applications where hardwire input/output connections are required

### System Requirements

- Use with SU10000RT3U and SU8000RT3U SmartOnline Hot-Swappable Modular UPS Systems

### Package Includes

- Hardwire PDU with Bypass Switch
- Mounting Hardware
- Owner's Manual

## Specifications

OVERVIEW	
Model Type	PDU Modules
Accessories Type	PDU Module
OUTPUT	
Frequency Compatibility	50 / 60 Hz



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Output Receptacles	Hardwire
Output Nominal Voltage	208/240V
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	208V AC; 240V AC
Input Connection Type	Hardwire
Voltage Compatibility (VAC)	208; 240
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	10.75 x 9 x 8
Shipping Dimensions (hwd / cm)	27.3 x 22.9 x 20.3
Shipping Weight (lbs.)	5.8
Shipping Weight (kg)	2.6
Unit Dimensions (hwd / in.)	5.25 x 7.5 x 6.5
Unit Dimensions (hwd / cm)	13.3 x 19.1 x 16.5
Unit Weight (lbs.)	4.6
Unit Weight (kg)	2.1
Material of Construction	Steel
<b>CERTIFICATIONS</b>	
Certifications	Tested to UL1778 (USA), CSA (Canada), RoHS compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.