

## Detachable PDU option with IEC output connections for compatible SmartOnline UPS Systems

MODEL NUMBER: **SUPDMB710IEC**



### Description

The SUPDMB710IEC converts the output of our SmartOnline SU8000RT3U and SU10000RT3U to worldwide output connections. Manual bypass feature ensures maximum availability of connected equipment while UPS maintenance occurs. Can accept input voltages of 200-240 VAC. Hardwire input/ 6 IEC320 C19 output connections.

### Features

- Converts the output of our SmartOnline SU8000RT3U and SU10000RT3U to worldwide output connections
- Manual bypass feature ensures maximum availability of connected equipment while UPS maintenance occurs
- Can accept input voltages of 200-240 VAC
- Hardwire input/ 6 IEC320 C19 output connections

## Specifications

OVERVIEW	
Model Type	Outlet Kits
Accessories Type	PDU Module
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) C19
Output Nominal Voltage	200/208/220/230/240 VAC
Overload Protection	6 double-pole 20A circuit breakers

### Highlights

- Converts compatible SmartOnline high-voltage UPS systems to provide worldwide compatible output connections
- For use with input voltages of 200-240 VAC
- Hardwired input/ 6 IEC320 C19 output connections
- Manual bypass feature ensures maximum equipment availability

### Applications

- Ideal for use with Tripp Lite's SU8000RT3U and SU10000RT3U UPS systems in 200-240V applications where hardwire input/ C19 output connections are required

### System Requirements

- For use with SmartOnline SU8000RT3U and SU10000RT3U Rack/Tower UPS systems in applications requiring a detachable PDU with manual bypass

### Package Includes

- SUPDMB710IEC detachable PDU
- Mounting hardware
- Owner's Manual with warranty instructions



<b>INPUT</b>	
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 230V AC; 240V AC; 220V AC
Input Connection Type	Hardwire
Voltage Compatibility (VAC)	200; 208; 220; 230; 240
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	12.25 x 9.25 x 8.25
Shipping Dimensions (hwd / cm)	31.1 x 23.5 x 21
Shipping Weight (lbs.)	9.9
Shipping Weight (kg)	4.5
Unit Dimensions (hwd / in.)	10.25 x 7.5 x 6.5
Unit Dimensions (hwd / cm)	26 x 19.1 x 16.5
Unit Weight (lbs.)	7.9
Unit Weight (kg)	3.6
Material of Construction	Sheet metal
<b>CERTIFICATIONS</b>	
Certifications	Tested to UL1778 (USA), CSA (Canada), CE (Europe)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.