

Protect It! 230V 6-Universal Outlet Surge Protector, 1.8M Cord, British Plug, 750 Joules

MODEL NUMBER: **SUPER6OMNIB**



Highlights

- 6 universal outlets
- 1.8 m power cord with British plug
- 750 joule rating
- Lighted on/off switch with integrated circuit breaker

Applications

- Ideal for any desktop, network or home computing application requiring AC surge suppression

Package Includes

- SUPER6OMNI B AC surge suppressor
- Instruction manual and warranty information

Description

Tripp Lite's Protect It!™ SUPER6OMNI B offers economical AC surge suppression for full protection of 220-250V workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. The SUPER6OMNI B offers 6 universal outlets and a 1.8 meter AC line cord with a British plug. AC suppression rated at 750 joules shields equipment from surges and line noise. Internal shutters also offer additional protection. Lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Right-angle outlets keep connected cords from blocking adjacent outlets. Attractive light gray high-impact housing.

INPUT: 1.8 m AC line cord with British plug

OUTPUT: 6 universal receptacles

ELECTRICAL: 220-250V AC, 50/60Hz, 10A

FORMAT: Corded multi-outlet strip

SUPPRESSION: - AC: 750 joules

Features

- Protect It!™ SUPER6OMNI B offers economical AC surge suppression
- 750 joules AC surge suppression shields equipment from surges and line noise
- 6 universal outlets protect computers and peripherals
- Internal shutters provide additional safety
- 1.8 m AC line cord with British plug
- Built-in power switch and 10 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Attractive light gray high-impact housing with keyhole mounting tabs allow versatile placement options
- Right-angle outlets keep connected cords from blocking adjacent outlets

Specifications



OVERVIEW	
Style	Strip
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) Universal outlets
Circuit Breaker (amps)	10
Overload Protection	10A resettable illuminated combo switch/circuit breaker
Outlet Orientation	right-angled
USB Charging	No
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Input Connection Type	British
Input Cord Length (ft.)	6
Input Cord Length (m)	1.8
Voltage Compatibility (VAC)	220-250
Maximum Surge Amps	13500
USER INTERFACE, ALERTS & CONTROLS	
Switches	Two position power switch
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	750
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (hwd / in.)	18.50 x 4.50 x 2.00
Shipping Dimensions (hwd / cm)	47.0 x 11.4 x 5.1



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (lbs.)	1.32
Shipping Weight (kg)	0.60
Unit Dimensions (hwd / in.)	15.50 x 2.50 x 1.25
Unit Dimensions (hwd / cm)	39.4 x 6.4 x 3.2
Unit Weight (lbs.)	1.0
Unit Weight (kg)	0.45
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Yes - slotted
Housing Color	Light Gray
Receptacle Color	Light Gray
Color (AC Line Cord)	light gray
Outlets Measurement (Center to Center)	51mm
Keyhole Slot Mounting Measurement (Center to Center)	219.5mm
SPECIAL FEATURES	
Right-Angle Plug	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.