

## 208/240V Single Phase Whip Extension cable in 20 ft. length with L6-30R output and L6-30P input

MODEL NUMBER: **SUWEL630C-20**



### Highlights

- 208/240V single phase whip extension cable
- 20 ft. length
- 3 conductor 10 AWG cable
- L6-30P plug, L6-30R outlet (208/240V 30A)

### Description

208/240V single phase whip extension cable with L6-30R outlet and L6-30P plug. 20 ft. length, 10 AWG.

### Features

- 208/240V single phase whip extension cable
- L6-30R outlet and L6-30P plug
- 20 ft. length
- 10 AWG

## Specifications

OVERVIEW	
Model Type	Whips
Accessories Type	Single-Phase Whip Cable
OUTPUT	
Monitored PDU options	PDUMNV30HV (0U / 4 C19, 20 C13 outlets)
Outlet Type	L6-30R
INPUT	
Input Connection Type	L6-30P
Cable Length (ft.)	20
Cable Length (m)	6.10



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

PHYSICAL	
Shipping Weight (lbs.)	8
Shipping Weight (kg)	3.6
Color	Black
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.