

## 208V 3-Phase Whip in 20 ft length with L21-20R output for 3-Phase Distribution Cabinet Applications

MODEL NUMBER: **SUWL2120C-20**



### Highlights

- 208V three phase whip distribution cabinet accessory
- 20 ft. length with 3 ft. removed outer jacket
- 5 conductor 12AWG stranded wire
- L21-20R outlet (208V 3PH 20A)

### Description

208V three phase whip with L21-20R outlet distributes power from 3 phase distribution cabinet to critical equipment racks. 20 ft. insulated and 3 ft. of removed outer jacket cabling supports hardwire connection to SUBB320 circuit breaker in SUDC208V series 3 phase distribution racks. L21-20R outlet is compatible with 208V loads and Power Distribution Units (PDUs) supporting a L21-20P plug-in connection.

### Features

- 208V three phase whip with L21-20R outlet
- Distributes power from 3 phase distribution cabinet to critical equipment racks
- 20 ft. insulated and 3 ft. of removed outer jacket cabling supports hardwire connection to SUBB320 circuit breaker in SUDC208V series 3 phase distribution racks
- L21-20R outlet is compatible with 208V loads and Power Distribution Units (PDUs) supporting a L21-20P plug-in connection

## Specifications

| OVERVIEW                 |   |
|--------------------------|---|
| Model Type               | Whips   |
| Accessories Type         | 3-Phase Whip Cable  |
| OUTPUT                   |   |
| PDU Recommendation Notes | Compatible with all PDU brands fitted with a L21-20P (208V 3PH 20A) input plug, including Tripp Lite <a href="#">PDU3MV6L2120</a> , <a href="#">PDU3MV6L2120B</a> , <a href="#">PDU3MV6L2120LV</a> , <a href="#">PDU3VN10L2120</a> , <a href="#">PDU3VN10L2120LV</a> , <a href="#">PDU3VN3L2120</a> , <a href="#">PDU3VN3L2120LV</a> , <a href="#">PDU3VSR10L2120</a> and <a href="#">PDU3VSR3L2120</a> |
| Outlet Type              | L21-20R (1)   |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

| INPUT                               |                                      |
|-------------------------------------|--------------------------------------|
| Input Connection Type               | Hardwire (5 wire - L1, L2, L3, N, G) |
| Cable Length (ft.)                  | 20                                   |
| Cable Length (m)                    | 6.1                                  |
| PHYSICAL                            |                                      |
| Shipping Weight (lbs.)              | 9.7                                  |
| Shipping Weight (kg)                | 4.4                                  |
| Unit Weight (lbs.)                  | 8.7                                  |
| Unit Weight (kg)                    | 3.9                                  |
| Color                               | Black                                |
| WARRANTY                            |                                      |
| Product Warranty Period (Worldwide) | 1-year limited warranty              |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.