

Protect It! 2-Outlet Surge Protector, 6-ft. Cord, 1080 Joules, 4 x USB Charging ports (4.8A total)

MODEL NUMBER: TLP26USBB



Description

Tripp Lite's TLP26USBB Charging Station provides exceptional convenience for daily charging tasks. Perfect for home, office, workstations and dorm rooms. With 2 AC outlets for safe power and 4 USB port with 4.8 amps of total power, this charging station can easily handle multiple devices. The built in slot can hold your tablet or phone for hands free viewing while charging. TLP26USBB charging station offers 2 total outlets, 6 foot cord, 4 USB charging ports for a total of 4.8 amps, and diagnostic LED to warn of suppressor damage. AC suppression rated at 1080 joules shields equipment from surges and line noise. . \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 6 NEMA5-15R/6-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet charging station

SUPPRESSION: AC: 150V RMS Clamping/1080 joules/400V UL60905

Features

- 2 outlets
- 6-ft. cord
- 4 USB charging ports - 4.8 amp total
- Built in slot to hold phones and tablets
- Surge suppression rating: 1080 joules
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker
- Green protection LED
- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Highlights

- 2 outlet / 6-ft. cord
- 1080 joule rating
- 4.8 amp quad port USB charger
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

- Ideal for any desktop, network or home computing application requiring AC line protection.
- USB charging ports offer fast charging for smartphones, tablets, MP3 players and other portable devices

Package Includes

- TLP26USBB charging station
- Instruction manual with warranty information

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| OVERVIEW | |
|------------------------------------|--|
| Style | Charging Station |
| OUTPUT | |
| Charging Ports / Amps | (4) 2.4A |
| Frequency Compatibility | 60 Hz |
| Output Receptacles | (2) 5-15R |
| Output (Watts) | 1560 |
| Circuit Breaker (amps) | 15 |
| USB Charging | Yes |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 120V (110-125V) |
| Input Connection Type | NEMA 5-15P |
| Input Cord Length (ft.) | 6 |
| Input Cord Length (m) | 1.83 |
| Input Cord Gauge Type | 14 gauge, SJT |
| Voltage Compatibility (VAC) | 120 |
| USER INTERFACE, ALERTS & CONTROLS | |
| Diagnostic LEDs | Built-in LED confirms suppressor "protection present" (green) status |
| SURGE / NOISE SUPPRESSION | |
| AC Suppression Joule Rating | 1080 |
| AC Suppression Response Time | < 1 ns |
| Protection Modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| UL1449 Let Through Rating | 400V |
| DATALINE SURGE SUPPRESSION | |
| Telephone/DSL Protection | No |
| Cable (Coax) Protection | No |
| Network (Ethernet) Protection | No |
| PHYSICAL | |
| Unit Dimensions (hwd / in.) | 1.42 x 5.21 x 5.21 |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|--|
| Unit Dimensions (hwd / cm) | 3.61 x 13.23 x 13.23 |
| Unit Weight (lbs.) | 1.2 |
| Unit Weight (kg) | .55 |
| Material of Construction | Plastic |
| Receptacle Color | Black |
| Color (AC Line Cord) | Black |
| Color | Black |
| SPECIAL FEATURES | |
| Right-Angle Plug | No |
| CERTIFICATIONS | |
| UL1449 3rd Edition (AC Suppression) | UL60905 |
| cUL / CSA (Canada) | cUL |
| Approvals | Exceeds IEEE 587 category A&B specifications |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$50,000 Ultimate Lifetime Insurance |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.