



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Protect It! 6-Outlet Surge Protector, 4-ft. Cord, 540 Joules - Accommodates 2 Transformers

MODEL NUMBER: **TLP64**



Highlights

- 6 outlets / 4 ft cord
- 540 joule rating
- \$20,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

Personal computers, CAD/CAM/CAE work stations, file servers, point-of-sale terminals and more.

Package Includes

- TLP64
- Instruction manual with warranty information

Description

Tripp Lite's TLP64 offers economical AC surge suppression for protection of workstations, desktop PCs, point-of-sale terminals and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. TLP64 offers 6 total outlets, 4 foot cord and diagnostic LEDs to warn of suppressor damage. AC suppression rated at 540 joules shields equipment from surges and line noise. Attractive gray suppressor housing with keyhole mounting tabs offer convenient protection of desktop computer equipment and accessories. \$20,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 6 outlets with integrated child safety covers
- 4ft cord
- Surge suppression rating: 540 joules
- EMI/RFI noise filtering
- Can accommodate up to 2 transformers without blocking remaining outlets
- Diagnostic LEDs indicate protection present and ground present
- Keyhole supports for wall mounting
- Lighted power switch
- \$20,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW	
Style	Strip
OUTPUT	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Frequency Compatibility	60 Hz
Output Receptacles	(6) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Overload Protection	15A resettable illuminated combo switch / circuit breaker
Transformer Accommodation	Supports 2 large transformer plug accessory without covering remaining outlets, accepts up to 4 transformers total
Outlet Safety Covers	6
Outlet Orientation	Block style 2 rows of 3 outlets
USB Charging	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Cord Length (ft.)	4
Input Cord Length (m)	1.22
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	36000
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Diagnostic LEDs	Built-in LED confirms suppressor "protection present" (green) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	540
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400v
EMI / RFI Filtering	Up to 40 dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Shipping Dimensions (hwd / in.)	11.02 x 7.08 x 1.77
Shipping Dimensions (hwd / cm)	27.99 x 17.98 x 4.50
Shipping Weight (lbs.)	1.65
Shipping Weight (kg)	0.75
Unit Dimensions (hwd / in.)	1.50 x 4.23 x 8.29
Unit Dimensions (hwd / cm)	3.81 x 10.74 x 21.06
Unit Weight (lbs.)	1.10
Unit Weight (kg)	0.50
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs enable wall mounting
Housing Color	Light Gray
Receptacle Color	Light Gray
Color (AC Line Cord)	Light Gray
Outlets Measurement (Center to Center)	Distance between standard outlets = 28.5mm; Distance between standard outlet and transformer outlet = 48.5mm
Keyhole Slot Mounting Measurement (Center to Center)	119mm
SPECIAL FEATURES	
Right-Angle Plug	No
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$20,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.