

Eco-Surge 6-Outlet Surge Protector, 6-ft. cord, 2100 Joules, Remote-Controlled

MODEL NUMBER: TLP66RCG



Highlights

- Keychain remote control turns GREEN energy saving outlets on/off
- 6 outlet/6-ft cord
- 2100 joules
- \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

Ideal for any desktop, network or home computing application requiring AC protection

Package Includes

- TLP66RCG ECO-SURGE Energy-Saving Surge Suppressor
- Owners Manual

Description

Tripp Lite's TLP66RCG offers reliable, GREEN surge technology that protects your computer and peripherals, the environment and your wallet. Energy-saving outlet configuration reduces energy waste (phantom loads) by cutting AC power to unused peripherals. Convenient, one-touch remote control turns green energy-saving outlets on and off. TLP66RCG has 6 total outlets, 6 foot cord and diagnostic LEDs to warn of wiring problems and suppressor damage. Network-grade AC suppression rated at 2100 joules shields equipment from surges and line noise. Attractive cool gray suppressor housing with keyhole mounting tabs and up to 4 transformer plug outlets offers convenient protection of desktop computer equipment and accessories. \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- Energy-saving outlet configuration reduces energy waste (phantom loads) by cutting AC power to unused peripherals
- 433 MHz key chain remote turns GREEN outlets on/off through walls, doors and furniture from up to 75 ft. away
- 6 total AC outlets with room for 4 transformer plugs
- 4 "Remote/Power Save" GREEN outlets cut AC power to idle components when turned off via remote control - perfect for intermittent use equipment like DVD players, gaming consoles, speaker systems, monitors, printers, lighting etc.
- Two "Switched/Always-On" outlets provide continuous power for devices such as DVRs (TiVo), cable and satellite boxes, modems, routers, external hard drives, cordless phones and fax machines
- 2100 joules of AC surge suppression shields equipment from the strongest surges and line noise
- Lighted power switch with integrated 15 amp circuit breaker offers power control and overload protection
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Attractive gray suppressor housing with keyhole mounting tabs allow versatile placement options
- \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Style	Strip
OUTPUT	
Output Watt Capacity (Watts)	1800
Frequency Compatibility	60 Hz
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	up to 4
USB Charging	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Plug Features	Straight plug
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	39000
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status and "receiver" (red)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2100
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
UL1449 Let Through Rating	400, 400, 400
EMI / RFI Filtering	Up to 20db
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Shipping Dimensions (hwd / in.)	13.19 x 6.30 x 1.89
Shipping Dimensions (hwd / cm)	33.50 x 16.00 x 4.80
Shipping Weight (lbs.)	1.73
Shipping Weight (kg)	0.78
Unit Dimensions (hwd / in.)	1.67 x 4.41 x 9.25
Unit Dimensions (hwd / cm)	4.24 x 11.20 x 23.50
Unit Weight (lbs.)	1.45
Unit Weight (kg)	0.66
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs enable wall mounting
Color (AC Line Cord)	Gray
Outlets Measurement (Center to Center)	Distance between "Remoted" outlets = 28.5mm; Distance between "Remoted" and "Switched" outlets = 50mm
SPECIAL FEATURES	
Green Energy-Saving Features	Power saving auto-shutoff ECO outlets
Right-Angle Plug	No
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.