

## Eco-Surge 7-Outlet, Surge Protector, 4-ft Cord, 1400 Joules, Timer-Controlled

MODEL NUMBER: TLP74TG



### Description

Tripp Lite's TLP74TG offers reliable, GREEN surge technology that protects your computer and peripherals as well as the environment and your wallet. Energy-saving outlet configuration reduces energy waste (phantom loads) by cutting AC power to unused peripherals. Convenient, multiple programmable timers allow users to set the exact time a device is turned on and off. The unit has 2 separate banks of outlets so you can program up to 20 timer options. The TLP74TG has 7 total outlets, 4 foot cord and diagnostic LEDs to warn of wiring problems and suppressor damage. Network-grade AC suppression rated at 1400 joules shields equipment from surges and line noise. Designed with an attractive cool gray suppressor housing, the TLP74TG provides 1 designated transformer outlet but can accommodate up to 4 transformer plug outlets offering convenient protection of desktop computer equipment and accessories. \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

### Features

- Energy-saving outlet configuration reduces energy waste (phantom loads) by cutting AC power to unused peripherals
- Programmable timer controls the output based on user settings. The timer can be set to automatically power connected ON and OFF based on time of day and day of the week for up to 20 possible timer settings.
- Two sets of timer-controlled outlet banks allow the user to connect equipment with varying timer settings.
- 1400 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- 7 surge-protected NEMA 5-15R AC outlets safeguard and entire home/business theater system while accommodating up to 4 large transformers
- 2 diagnostic LEDs alert user to protection and grounded status
- Lighted on/off switch with integrated circuit breaker - protects against dangerous system overload
- \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

## Specifications

### Highlights

- Timer-controlled outlets
- Two separate outlet banks
- 1400 joules
- 7 outlet / 4-ft cord
- Diagnostic LEDs
- \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

### Applications

- Perfect for small-to-medium home/business, lighting installations, entertainment systems, satellite and A/V receivers, DVD/CD players and more

### Package Includes

- TLP74TG ECO-SURGE Home/Business Theater Surge Suppressor
- Instruction manual with warranty information



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|  |   |
|--|---|
| Style  | strip   |
| <b>OUTPUT</b>                                |   |
| Output Volt Amp Capacity (VA)                | 15  |
| Output Watt Capacity (Watts)                 | 1875  |
| Frequency Compatibility                      | 60 Hz   |
| Output Receptacles                           | (7) 5-15R   |
| Outlet Type                                  | NEMA 5-15R  |
| Transformer Accommodation                    | 1 Designated transformer outlet but can accommodate up to 4                               |
| USB Charging                                 | No  |
| <b>INPUT</b>                                 |   |
| Nominal Input Voltage(s) Supported           | 120V AC   |
| Recommended Electrical Service               | 120V (110-125V)   |
| Input Connection Type                        | NEMAP - NEMA5-15P   |
| Input Cord Length (ft.)                      | 4   |
| Input Cord Length (m)                        | 1.22  |
| Input Cord Gauge Type                        | 14 AWG 3C SJT   |
| Voltage Compatibility (VAC)                  | 120   |
| Maximum Surge Amps                           | 19500   |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |   |
| Front Panel LCD Display                      | AM/PM LCD Clock   |
| Switches                                     | Combination AC circuit breaker and 2 position lighted on/off power switch                 |
| LED Indicators                               | Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status |
| <b>SURGE / NOISE SUPPRESSION</b>             |   |
| AC Suppression Joule Rating                  | 1400  |
| AC Suppression Response Time                 | < 1 ns  |
| Protection Modes                             | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression.       |
| Clamping Voltage (RMS)                       | 150   |
| UL1449 Let Through Rating                    | 400   |
| EMI / RFI Filtering                          | up to 20dB  |
| <b>DATALINE SURGE SUPPRESSION</b>            |   |
| Telephone/DSL Protection                     | No  |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|  |  |
|--|--|
| Cable (Coax) Protection                                    | No   |
| Network (Ethernet) Protection                              | No   |
| <b>PHYSICAL</b>  |  |
| Shipping Dimensions (hwd / in.)                            | 13.4 x 5.51 x 1.96   |
| Shipping Dimensions (hwd / cm)                             | 34.04 x 14.00 x 4.98   |
| Shipping Weight (lbs.)                                     | 1.5  |
| Shipping Weight (kg)                                       | 0.68   |
| Unit Dimensions (hwd / in.)                                | 1.56 x 3.54 x 11.22  |
| Unit Dimensions (hwd / cm)                                 | 3.96 x 8.99 x 28.50  |
| Unit Weight (lbs.)   | 1.43   |
| Unit Weight (kg)   | 0.65   |
| Material of Construction                                   | plastic  |
| Color (AC Line Cord)                                       | gray   |
| Outlets Measurement (Center to Center)                     | Distance between standard outlets = 28.5mm; Distance between standard outlet and transformer outlet = 57mm |
| <b>SPECIAL FEATURES</b>                                    |  |
| Green Energy-Saving Features                               | Schedulable daily hours of economy mode operation  |
| Right-Angle Plug   | No   |
| <b>CERTIFICATIONS</b>                                      |  |
| UL1449 3rd Edition (AC Suppression)                        | UL1449 3rd Edition   |
| UL1363 (Power Tap)   | UL1363   |
| UL497A (Communications)                                    | UL497A   |
| FCC Part 68 (Communications)                               | FCC Part 68  |
| cUL / CSA (Canada)   | cUL  |
| Approvals  | Exceeds IEEE 587 category A&B specifications   |
| <b>WARRANTY</b>  |  |
| Product Warranty Period (Worldwide)                        | Lifetime limited warranty  |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$75,000 <a href="#">Ultimate Lifetime Insurance</a>   |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.