

## Protect It! 7-Outlet Surge Protector, 6-ft. Cord, 1080 Joules, Modem/Fax Protection, Black Housing

MODEL NUMBER: TLP76RBTEL



### Highlights

- 7 outlets (6 right-angle outlets and 1 designated transformer outlet)
- 6-ft. cord
- 1080 joule rating
- Modem/fax surge protection
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

### Applications

- Ideal for any desktop, network or home computing application requiring AC line protection.

### Package Includes

- TLP76RBTEL Surge Suppressor

### Description

Tripp Lite's TLP76RBTEL surge suppressor offers complete AC and phone line surge suppression for protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. Set of RJ11 telephone line suppression jacks protect dialup and DSL modem lines, fax machines, cordless phones and more. TLP76RBTEL offers 7 total outlets (6 at right angle and 1 designated transformer plug outlet), 6 foot cord and diagnostic LED to warn of suppressor damage. AC suppression rated at 1080 joules shields equipment from surges and line noise. Attractive black housing with keyhole mounting tabs offering convenient protection of desktop computer equipment and accessories. \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 7 NEMA5-15R/4-ft. AC line cord

ELECTRICAL: 120V AC, 60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip

SUPPRESSION: AC: 150V RMS Clamping/540 joules/400V UL1449 Let-through

### Features

- 1080 joules AC surge suppression shields equipment from the strongest surges and line noise
- 7 total AC outlets (6 right angle and 1 transformer plug outlet)
- 6 foot AC line cable
- Phone line surge suppression protects both dialup and DSL modems, plus fax machines, cordless phones and more
- Attractive black housing
- Lighted on/off switch with integrated circuit breaker for overload protection of all outlets
- Diagnostic LED confirms surge suppression status
- Integrated keyhole slots provide convenient wall/desk mounting
- UL1449 3rd Edition Rated (400V all modes), UL1363 (Power Tap), cUL (Canada)
- Exceeds IEEE 587 category A & B surge suppression specifications
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)



## Specifications

| OVERVIEW                           |  |
|------------------------------------|--|
| Style                              | Strip  |
| OUTPUT                             |  |
| Frequency Compatibility            | 60 Hz  |
| Output Receptacles                 | (7) 5-15R  |
| Output (Watts)                     | 1800   |
| Circuit Breaker (amps)             | 15   |
| Transformer Accommodation          | Supports 1 large transformer plug accessory without covering remaining outlets     |
| Outlet Orientation                 | Single row   |
| USB Charging                       | No   |
| INPUT                              |  |
| Nominal Input Voltage(s) Supported | 120V AC  |
| Recommended Electrical Service     | 120V (110-125V)  |
| Input Connection Type              | NEMA 5-15P   |
| Input Cord Length (ft.)            | 6  |
| Input Cord Length (m)              | 1.83   |
| Input Cord Gauge Type              | 14 gauge, SJT  |
| Voltage Compatibility (VAC)        | 120  |
| Maximum Surge Amps                 | 36000  |
| USER INTERFACE, ALERTS & CONTROLS  |  |
| Switches                           | Combination AC circuit breaker and 2 position on/off power switch                  |
| Diagnostic LEDs                    | Built-in LED confirms suppressor "protection present" (green) status               |
| SURGE / NOISE SUPPRESSION          |  |
| AC Suppression Joule Rating        | 1080   |
| AC Suppression Response Time       | < 1 ns   |
| Protection Modes                   | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| Clamping Voltage (RMS)             | 150  |
| UL1449 Let Through Rating          | 400V   |
| DATALINE SURGE SUPPRESSION         |  |
| Telephone/DSL Protection           | Yes  |



Tripp Lite  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

|  |  |
|--|--|
| Cable (Coax) Protection                                    | No   |
| Network (Ethernet) Protection                              | No   |
| <b>PHYSICAL</b>  |  |
| Shipping Dimensions (hwd / in.)                            | 14.05 x 3.26 x 1.37                                  |
| Shipping Dimensions (hwd / cm)                             | 35.69 x 8.28 x 3.48                                  |
| Shipping Weight (lbs.)                                     | 1.5  |
| Shipping Weight (kg)                                       | .68  |
| Unit Dimensions (hwd / in.)                                | 1.32 x 2.05 x 12.51                                  |
| Unit Dimensions (hwd / cm)                                 | 3.35x x5.21 x 31.78                                  |
| Unit Weight (lbs.)   | 1.21   |
| Unit Weight (kg)   | 0.55   |
| Material of Construction                                   | Plastic  |
| Integrated Keyhole Mounting Tabs                           | Keyhole mounting tabs enable wall mounting           |
| Color (AC Line Cord)                                       | Black  |
| Color  | Black  |
| Outlets Measurement (Center to Center)                     | 28.5mm   |
| Keyhole Slot Mounting Measurement (Center to Center)       | 207mm  |
| <b>SPECIAL FEATURES</b>                                    |  |
| Right-Angle Plug   | No   |
| <b>CERTIFICATIONS</b>                                      |  |
| UL1449 3rd Edition (AC Suppression)                        | UL1449 3rd Edition                                   |
| UL1363 (Power Tap)   | UL1363   |
| cUL / CSA (Canada)   | cUL  |
| Approvals  | Exceeds IEEE 587 category A&B specifications         |
| <b>WARRANTY</b>  |  |
| Product Warranty Period (Worldwide)                        | Lifetime limited warranty                            |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$50,000 <a href="#">Ultimate Lifetime Insurance</a> |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.